

1.6ft (50cm) USB-A to USB-C Charging Cable, Charge & Sync, 3A, USB 2.0 - USB Charging Cord

Product ID: USB2AC50CM



This USB-C to USB-A cable makes it easy to charge and sync USB Type-C mobile devices using the USB-A port on your computer or a standard USB-A wall charger, car charger or power bank.

This non-standard 0.5-meter cable is great for close-range connections to charge and sync your USB Type-C mobile devices from your laptop.

You can also use the cable to charge your USB-C devices from a USB-A wall charger, car charger or power bank. It's the ideal cable for commuters, for in-car use or to reduce clutter when syncing with your laptop.

Replace the USB-C charging cable that came with your device or keep one as a spare in your laptop bag, backpack or other carrying case.

Certifications, Reports and Compatibility



Applications

- Charge and sync your USB-C mobile digital devices
- Charge your USB-C devices with a USB-A wall charger, car charger or power bank

Features

- Offers 0.5 meters in cable length for close-range connections

- Convenient, reversible USB-C connector makes every connection easy
- Guaranteed reliability with our lifetime warranty

Hardware

| | |
|-----------------------|--------------------------------|
| Warranty | Lifetime |
| Connector Plating | Nickel |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

Performance

| | |
|---------------|----------------------|
| Type and Rate | USB 2.0 - 480 Mbit/s |
|---------------|----------------------|

Connector(s)

| | |
|-------------|---|
| Connector A | 1 - USB 2.0 Type-A (4 pin, 480Mbps) |
| Connector B | 1 - USB Type-C (24-pin) USB 2.0 (480Mbps) |

Environmental

| | |
|-----------------------|-----------------------------|
| Operating Temperature | 0C to 35C (32F to 95F) |
| Storage Temperature | -10C to 80C (14F to 176F) |
| Humidity | 5%-80% RH (no condensation) |

Physical Characteristics

| | |
|-------------------|-----------------|
| Color | Black |
| Connector Style | Straight |
| Wire Gauge | 22/30 AWG |
| Cable Length | 1.6 ft [0.5 m] |
| Product Length | 1.6 ft [0.5 m] |
| Product Width | 0.6 in [1.5 cm] |
| Product Height | 0.3 in [0.7 cm] |
| Weight of Product | 0.2 oz [6.0 g] |

**Packaging
Information**

| | |
|------------------------------|------------------|
| Package Quantity | 1 |
| Package Length | 4.9 in [12.5 cm] |
| Package Width | 5.2 in [13.3 cm] |
| Package Height | 0.6 in [1.4 cm] |
| Shipping (Package) Weight | 1.1 oz [32.0 g] |

What's in the Box

| | |
|---------------------|--------------------------|
| Included in Package | 1 - USB-C to USB-A cable |
|---------------------|--------------------------|

**Warranty
Information**

| | |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

**Product appearance and specifications are subject to change without notice.*

