

Micro-USB Cable with Right-Angled Connectors - M/M - 2m (6ft)

Product ID: USB2AUB2RA2M



This Micro-USB cable features two right-angled connectors that let you connect to hard-to-reach ports and also help prevent cable and port damage. The cable is great for charging your mobile devices in a car, or for connecting to peripherals that may be difficult to connect to when using a straight connection.

Connect to hard-to-reach ports

The right-angled connectors allow you to connect to ports that may otherwise be inaccessible or difficult to reach. Perfect for charging car-mounted mobile devices or for connecting your portable hard drive or other Micro-USB 2.0 device to your computer in such a way that it fits your installation needs.

The angled connectors prevent the cable from bending awkwardly or from straining too much to make a connection. It offers a more natural fit at the connection points, preventing unnecessary stress and damage to the cable and ports.

Charge and sync your USB 2.0 mobile devices

Charge your USB 2.0 Micro B-equipped phones and tablets with full charging power, with no increase in charge time -- even at a distance of 6 feet (2 meters) away from your charger.

The long cable overcomes distance restrictions and lets you stay connected even while you're taking notes in a boardroom, catching up on emails in a hotel room, or reading in a coffee shop.

Connect to your mobile devices with ease

The cable features a thin, yet sturdy connector molding, so you'll be able to connect to your phone or tablet without removing its protective case. Plus, the cable's right-angled Micro-USB connector lets you text, work or game on your mobile device even while it's charging, without the cable getting in the way.

The USB2AUB2RA2M 2-meter cable is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Charge and sync your Micro-USB mobile devices
- Connect your Micro-USB 2.0 devices, such as an external hard drive, to your PC or laptop

Features

- Connect to your device and your computer or charger even in hard to reach areas and tight spaces
- Position your USB 2.0 devices as needed throughout your workspace
- Guaranteed reliability with our lifetime warranty

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB Micro-B (5 pin)

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

Physical Characteristics

Color	Black
Connector Style	Right Angled
Wire Gauge	24/30 AWG
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]
Product Width	1.0 in [2.6 cm]
Product Height	0.3 in [0.8 cm]
Weight of Product	1.6 oz [44.0 g]

Packaging Information

Package Quantity	1
Package Length	5.3 in [13.5 cm]
Package Width	5.0 in [12.6 cm]
Package Height	0.8 in [2.0 cm]
Shipping (Package) Weight	1.7 oz [48.0 g]

What's in the Box

Included in Package	1 - 2m Right-Angled Micro USB 2.0 Cable
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

