

10ft White USB-C Charging Cable, USB-IF Certified USB C Cable, 240W PD EPR, USB 2.0 Type-C Laptop Charger Cord, USB-C Data Transfer Cable, TPE Jacket

**Product ID:** USB2EPR10FW



Connect a charger to a USB Power Delivery (PD) 3.1-enabled device, using this USB-C Charging Cable. The USB-C charger cord delivers up to 240W of Extended Power Range (EPR) Power Delivery and 5A output for fast charging. The connector markings enable quick visual identification, distinguishing this cable from other similar-looking or unmarked USB-C cables. Eliminate guesswork and always choose the appropriate Type-C cable to support full 240W charging.

Designed for frequent use, the USB-C EPR Charging Cable features a rugged TPE outer jacket for increased wear resistance. The durable nickel-plated connectors are rated to operate beyond 10,000 insertion cycles, enhancing its durability and longevity.

Charge a USB-C device with a USB-C wall charger, car charger, or power bank. The 10-foot (3-meter) USB Type-C cable is longer than standard USB-C charging cables and is ideal for larger desk and mobile workspaces where extra reach is required.

With up to 5A of output, the USB-C Charger Cord supports up to 240W of Power Delivery to charge a USB-C laptop, or fast charge a tablet or smartphone. To use, connect the cable from a USB-C laptop to a USB-C wall charger.

## Certifications, Reports and Compatibility



## Applications

- Ideal for high-power USB-C devices

- USB-IF Certified for guaranteed reliability

## Features

- **USB-C EPR CHARGING CABLE:** Type-C cable supports Power Delivery 3.1 Extended Power Range (EPR); Up to 240W to high-power USB-C laptops; 10ft length provides extra reach; Connector markings identify data/power specs; Choose the right 240W cable at-a-glance
- **USB-IF CERTIFIED:** The USB C Cable is USB-IF certified with integrated E-marker chip, for consistent Power Delivery output to USB-C hosts and peripherals; When using certified cables, reliable performance and compatibility is guaranteed
- **QUALITY CONSTRUCTION:** Nickel-plated connectors rated beyond 10,000 insertions; Thicker 24AWG wire for consistent power; Withstands 120° bends; Braided Aluminum shield protects from EMI; Durable TPE outer jacket is halogen-free and RoHS compliant
- **APPLICATIONS:** Compatible with USB-C Power Delivery-enabled devices; Ideal for high-power laptops requiring EPR charging, including 16in MacBook Pro M3 Pro/M3 Max; Supports USB 2.0 for general use, including file transfer and device synchronization
- **PERFORMANCE:** 240W/5A PD 3.1 EPR, 48V; Backward Compatible w/140W/100W/60W; USB 2.0 Type-C (480Mbps); 10-foot (3-meter) cable; Color: White; O.D.: 0.16in (4.0mm); TPE Jacket w/Braided Aluminum Shield; NOTE: USB-C video (DP Alt Mode) is not supported

---

### Hardware

	Warranty	Lifetime
Active or Passive Adapter	Passive	
Connector Plating	Nickel	
Cable Jacket Material	TPE - Thermoplastic Elastomers	
Cable Shield Material	Aluminum-Mylar Foil with Braid	
Cable Type	Passive Copper Cable	

---

### Performance

Maximum Data Transfer Rate	480Mbps
Type and Rate	USB 2.0 - 480 Mbit/s
MTBF	Rated beyond 10,000 insertion cycles

---

### Connector(s)

Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
-------------	---

---

Connector B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
-------------	---

---

**Special Notes / Requirements**

Note	USB-C video (DP Alt Mode) is not supported
------	--

---

**Power**

Power Source	Bus Powered
Power Delivery	240W
Input Current	5A

---

**Environmental**

Operating Temperature	-10 to 60 (14&degF to 140&degF)
Storage Temperature	-20 to 70 (-4&degF to 158&degF)
Humidity	5%~85%

---

**Physical Characteristics**

Color	White
Connector Style	Straight
Wire Gauge	24 AWG
Material	Polyamide Resin
Cable Length	10.0 ft [3.0 m]
Cable OD	0.2 in [4 mm]
Product Length	10.0 ft [3.0 m]
Product Width	0.5 in [1.2 cm]
Product Height	0.3 in [6.4 mm]
Weight of Product	3.3 oz [94 g]

---

**Packaging Information**

Package Length	4.8 in [12.1 cm]
Package Width	4.9 in [12.5 cm]

Package Height 1.1 in [2.8 cm]

Shipping (Package) Weight 5.3 oz [150.0 g]

---

**What's in the Box**

Included in Package 1 - 10ft USB-C Charging Cable M/M

---

**Warranty  
Information**

Warranty Lifetime

---

*\*Product appearance and specifications are subject to change without notice.*

