

25 ft Coax High Resolution Monitor VGA Cable with Audio HD15 M/M

Product ID: MXTHQMM25A



The MXTHQMM25A 25-foot High Resolution VGA Monitor Cable with Audio is a high quality SVGA cable designed to provide the highest video quality possible through VGA - a single cable solution, for connecting both video between a VGA video card and monitor, and audio connections between a sound card and external audio device.

StarTech.com's high resolution VGA cable with audio features high quality male-to-male coaxial VGA cable, and is designed to eliminate picture ""ghosting"" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

The 25-foot SVGA cable (VGA Cable with Audio) is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Make video and audio connections using a single cable
- Ideal for high resolution VGA monitors (1920x1200 and above)

Features

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color

- Molded connector ends with strain relief
- Ferrite core eliminates EMI interference

Hardware

Warranty	Lifetime
Number of Conductors	15
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	2
Regulatory Approvals	UL2919

Performance

Impedance	75 Ohm
-----------	--------

Connector(s)

Connector A	1 - 3.5 mm Mini-Jack (3 Position)
	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - 3.5 mm Mini-Jack (3 Position)
	1 - VGA (15 pin, High Density D-Sub)

Environmental

Operating Temperature	0 to 60 C
Storage Temperature	-20 to 80 C
Humidity	0 - 80 %RH

Physical Characteristics

Color	Black
Connector Style	Straight

Wire Gauge	28 AWG
Cable Length	25.0 ft [7.6 m]
Product Length	25.0 ft [7.6 m]
Weight of Product	29.6 oz [839 g]

Packaging Information

Package Quantity	1
Package Length	8.0 in [20.2 cm]
Package Width	8.6 in [21.9 cm]
Package Height	2.7 in [6.8 cm]
Shipping (Package) Weight	1.9 lb [0.8 kg]

What's in the Box

Included in Package	1 - 25 ft Coax High Resolution Monitor VGA Cable with Audio HD15 M/M
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

