

3ft (1m) USB-A to USB-C Charging Cable, USB 10Gbps, Charge & Sync, 3A, USB-IF Certified - USB Charging Cord

**Product ID:** USB31AC1M



This USB to USB-C cable lets you connect your USB-C devices to the USB-A port on a computer or charger.

This USB-A to USB-C cable has been certified by USB-IF (USB Implementers Forum) to meet all USB 3.2 Gen 2 specifications. This includes all environmental, electrical and mechanical standards set for USB compliance, ensuring a high-quality, reliable cable for all of your USB-C devices.

Move large files or transfer movies in seconds with this USB 3.2 Gen 2 cable that supports data transfer speeds of up to 10Gbps when connected to a host computer that supports 10Gbps..That's twice the speed of USB 3.2 Gen 1 and 20x faster than USB 2.0.

StarTech.com offers PCIe cards with 10Gbps USB-A ports. We also offer a Thunderbolt 3 controller adapter for adding 10Gbps ports to your Thunderbolt 3 laptop.

The USB to USB-C cable is perfect for people on the move -- you can charge your device from anywhere.

- Wall charger
- Car charger
- Power bank
- Laptop

The cable also lets you connect newer USB 3.2 Gen 2, USB-C peripherals, such as hard drive enclosures and docks to devices with a USB-A port.

## Certifications, Reports and Compatibility



## Applications

- Connect USB-C devices to the USB-A port on a computer or charger

## Features

- Provide high-quality connections with a USB-IF certified USB to USB-C cable
- Transfer data faster with this USB 3.2 Gen 2 cable that supports 10Gbps data transfer speeds
- Charge your USB-C mobile devices with a USB-A charger or laptop
- Connect newer USB-C peripherals to laptops that are not equipped with USB-C ports

### Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

### Performance

Type and Rate	USB 3.2 Gen 2 - 10 Gbit/s
---------------	---------------------------

### Connector(s)

Connector A	1 - USB 3.2 Type-A (9 pin, Gen 2, 10Gbps)
Connector B	1 - USB 3.2 Type-C (24 pin, Gen 2, 10Gbps)

### Environmental

Operating Temperature	0C to 35C (32F to 95F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	5%-80% RH (no condensation)

### Physical Characteristics

Color	Black
-------	-------

---

Connector Style	Straight
Cable Length	3.3 ft [1 m]
Product Length	3.3 ft [1.0 m]
Product Width	0.6 in [1.6 cm]
Product Height	0.3 in [0.8 cm]
Weight of Product	1.4 oz [40.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	5.1 in [13.0 cm]
Package Width	5.0 in [12.7 cm]
Package Height	0.7 in [1.9 cm]
Shipping (Package) Weight	1.7 oz [48.0 g]

---

**What's in the Box**

Included in Package	1 - 1m USB 3.1 USB-C to USB-A Cable
---------------------	-------------------------------------

---

**Warranty Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

