

6 ft Black SuperSpeed USB 3.0 (5Gbps) Cable A to A - M/M

Product ID: USB3SAA6BK



StarTech.com's 6ft Black USB 3.2 Gen 1 cable (A-A) offers a durable, high quality connection that harnesses the full capability of the SuperSpeed USB 3.2 Gen 1 standard.

Designed for next-generation SuperSpeed USB device connections, this USB 3.2 Gen 1 A to A Male/Male cable provides connectivity between a PC and hub or other USB A devices, delivering a throughput of up to 5Gbps when used with a USB 3.2 Gen 1 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 6ft USB 3.2 Gen 1 A to A device cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 6ft USB 3.2 Gen 1 device cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certifications, Reports and Compatibility



Applications

- Connect a USB 3.0 SuperSpeed A devices such as a USB hub to a Desktop or Server

Features

- Designed and constructed to SuperSpeed USB 3.2 Gen1 Specifications
- Molded connectors with strain relief

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Foil shielded twisted pair

Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

Connector(s)

Connector A	1 - USB Type-A (9 pin, 5 Gbps)
Connector B	1 - USB Type-A (9 pin, 5 Gbps)

Environmental

Operating Temperature	-10C to 50C (14F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0~75% RH

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.5 in [1.4 cm]
Product Height	0.5 in [1.2 cm]
Weight of Product	0.7 oz [21.0 g]

Packaging Information

Package Quantity	1
Package Length	6.4 in [16.3 cm]
Package Width	5.0 in [12.7 cm]

Package Height 1.1 in [2.7 cm]

Shipping (Package) Weight 3.1 oz [88.0 g]

What's in the Box

Included in Package 1 - USB A to A Male to Male cable

**Warranty
Information**

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*

