

15ft (4.5m) Computer Power Cord, NEMA 5-15P to C13, 10A 125V, 18AWG, Black Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable - UL Listed

Product ID: PXT10115



The PXT10115 15-foot Computer Power Cord is a durable, universal power cord that can be used as a cost effective replacement for your existing PC power cord, and enables you to extend the connection distance between a computer or peripheral device and an available power outlet by 15ft.

StarTech.com's 15ft Computer Power cable lets you plug a monitor, PC, or laser printer into a grounded power outlet and is backed by StarTech.com's lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Plugs monitor, PC, or laser printer into a grounded power outlet

Features

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability 3 Conductor Power Cable made from 100% Copper Wire Fire Rating: VW-1
- **SPECS:** 15ft (4.5m) Power Cable NEMA 5-15P to IEC 60320 C13 18AWG 125V 10A (Max) Jacket Rating: SVT Jacket Material: PVC Color: Black Temperature Range: 37F to 140F (3 to 60) Cable Outer Diameter: 0.25in (6.3mm)

- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more Replacement PC power supply cable/cord

- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance This C13 power cord is available in other lengths

Hardware

Warranty	Lifetime
Number of Conductors	3

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C13 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	10A

Environmental

Operating Temperature	0C to 60C (32F to 140F)
-----------------------	-------------------------

Physical Characteristics

Color	Black
Wire Gauge	18 AWG
Cable Length	15.0 ft [4.6 m]
Product Length	15.0 ft [4.6 m]
Product Width	1.0 in [2.5 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	11.3 oz [320.0 g]

Packaging Information

Package Quantity	1
Package Length	6.7 in [16.9 cm]
Package Width	7.7 in [19.6 cm]
Package Height	1.5 in [3.8 cm]
Shipping (Package) Weight	11.4 oz [322.0 g]

What's in the Box

Included in Package	1 - 15ft Standard Computer Power Cord - NEMA5-15P to C13
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

