

3ft (1m) Power Extension Cord - 360° Rotating Flat Plug Extension Cord - NEMA 5-15P to NEMA 5-15R, 16 AWG, 125V/13A - Black Short 3-Prong Power Extender Cable

**Product ID:** RTPAC1013



This 3 ft. Power Extension Cord features a rotating NEMA 5-15P to NEMA 5-15R connectors, maximizing the space available on your power strip, surge protector, or wall outlet.

Featuring a 360 rotating flat plug, this power cord extender enables you to easily connect your devices without damaging the cord. The flat plug design provides a convenient solution when connecting your devices in tight spaces.

The additional length provided by this three-foot cord allows for cleaner cable management when connecting powered devices.

Constructed with high-quality materials, the NEMA power cable is built with a 16 AWG wire suitable for high power connections.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

RTPAC1013 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Extend the connection distance between your PC, monitor, laser printer or scanner

## Features

- 360 ROTATING PLUG EXTENSION CABLE:** The 360 degree rotating flat plug extension cord can be positioned at any angle in tight areas; Ideal for use in a wall outlet or maximize space on power bars without blocking or interfering w/ other outlets
- CONVENIENT FLAT PLUG:** Power extension cord w/ flat power plug design is ideal for wall sockets in space constrained areas such as behind desks or furniture close to the wall; Save more space in your home office setup by moving furniture closer to the wall
- CERTIFIED POWER CORD:** This short 3ft extension cable with 16AWG wires is UL certified to ensure maximum safety for your devices and provide reliable power supply for all your electronics; 3-pronged plug with grounding wire provides additional protection
- DURABLE:** Long lasting PVC connectors to withstand everyday use; Unique rotating mechanism designed for noise-free power; PVC jacket with flexible strain relief prevents cable fraying/damage; Ideal for IT equipment/appliances, computers, monitors, etc
- SPECS:** Length: 3 foot power extender cord NEMA 5-15P (Plug) to (NEMA 5-15R (Socket) 16AWG 125V, 13A (Max) Cable OD: 0.33" Jacket: PVC Color: Black Lifetime Warranty

---

### Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

---

### Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - NEMA 5-15 Power (North America)

---

### Power

Input Voltage	125 AC
Input Current	13 A

---

### Environmental

Operating Temperature	0C to +40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0% to 90% RH

---

**Physical Characteristics**

Color	Black
Connector Style	Straight
Wire Gauge	16 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	3.4 ft [1.0 m]
Product Width	1.5 in [3.9 cm]
Product Height	1.4 in [3.6 cm]
Weight of Product	6.1 oz [172.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	11.3 in [28.7 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.0 in [2.5 cm]
Shipping (Package) Weight	6.3 oz [178.0 g]

---

**What's in the Box**

Included in Package	1 - 3 ft. Rotating Power Cord Extension - NEMA 5-15R/P
---------------------	--

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*