

6ft (2m) USB-C Charging Cable, Durable and Ultra-Flexible, Side Screw Locking, 240W (5A) PD EPR, USB 2.0 Laptop Charger Cable, USB-IF Certified, Rugged USB-C Charging Cord

**Product ID:** S2CEPR2M-USBSL-CABLE



Connect a charger or hub to a USB Power Delivery (PD) 3.1-enabled device, using this USB-C Charging Cable. The USB-C charger cord delivers up to 240W of Extended Power Range (EPR) Power Delivery and 5A output for fast charging. The connector markings enable quick visual identification, distinguishing it from other similar-looking or unmarked USB-C cables. Eliminate guesswork and always choose the right Type-C cable to support full 240W charging.

#### Screw Locking USB-C

This cable features dual locking screws that can securely connect to your USB-C peripherals and can prevent accidental disconnection from your devices. The knurled screws can be removed from the cable completely allowing it to be used as a standard USB-C cable if required.

The screws are designed to fit all devices that use a standard side screw locking input.

#### Quality Construction

The USB-C EPR Charging Cable features a silicone inner jacket with a braided nylon exterior for optimal flexibility and wear protection. The durable nickel-plated connectors are designed for frequent daily use, and are rated to operate beyond 20,000 insertion cycles.

#### Charge Mobile Devices On The Go

Charge a USB-C device with a USB-C wall charger, car charger, or power bank. The 2-meter (6.6-foot) USB Type-C cable is the ideal length for desk and mobile workstations, commuters, in-car use or to reduce clutter when syncing with a USB-C laptop.

#### Power a Laptop

With up to 5A of output, the USB-C Charger Cord supports up to 240W of Power Delivery to charge a USB-C laptop, or fast charge a tablet or smartphone. To use, connect the cable from a USB-C laptop to a USB-C wall charger.

## Certifications, Reports and Compatibility



## Applications

### Features

- **USB-C EPR CHARGING CABLE:** Side Screw Locking USB-C cable supports Power Delivery 3.1 EPR with up to 240W for high-performance laptops; Ideal for chargers and hubs with side-locking USB-C ports; Performance markings on connectors for easy identification
- **USB-IF CERTIFIED:** The USB C Cable with integrated E-marker chip is USB-IF certified, for consistent Power Delivery output to USB-C hosts and peripherals; When using certified cables, reliable performance and compatibility is guaranteed
- **QUALITY CONSTRUCTION:** Flexible braided nylon jacket resists wear, withstands 90 bends and up to 20,000 bending cycles; Nickel-plated connectors rated beyond 10,000 insertions; M2 Screw Locking connector with knurled grip for easy installation and removal
- **APPLICATIONS:** Compatible with USB-C Power Delivery-enabled devices; Screw Locking for drive enclosures and external storage; Suitable for high-performance laptops such as 16in MacBook Pro Max M-series; Supports USB 2.0 for general file transfer or sync
- **PERFORMANCE:** 240W (5A) PD 3.1 EPR, 48V; Compatible with 140W, 100W, 60W; USB 2.0 Type-C (480Mbps); 2-meter (6.6-foot) cable; Color: Black; O.D.: 0.18in (4.7mm); Silicone Jacket w/Braided Nylon; NOTE: USB-C video (DP Alt Mode) not supported

---

### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	Silicone with Braided Nylon

---

### Performance

MTBF	Rated beyond 10,000 insertions
------	--------------------------------

---

### Connector(s)

Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)

---

**Power**

Power Delivery	240W
----------------	------

---

**Environmental**

Operating Temperature	0&degC - 50&degC (32&degF - 122&degF)
Storage Temperature	-20&degC - 70&degC (-4&degF - 158&degF)
Humidity	5% - 85%

---

**Physical Characteristics**

Color	Black
Connector Style	Straight
Wire Gauge	30 AWG
Material	ABS
Cable Length	6.6 ft [2 m]
Cable OD	0.2 in [4.7 mm]
Product Length	6.6 ft [2.0 m]
Product Width	0.8 in [1.9 cm]
Product Height	0.3 in [6.9 mm]
Weight of Product	3.0 oz [86 g]

---

**Packaging Information**

Package Length	5.0 in [12.8 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.5 in [1.4 cm]
Shipping (Package) Weight	3.2 oz [90.0 g]

---

**What's in the Box**

Included in Package	1 - 2m USB-C Charging Cable M/M - Side Locking
---------------------	--

---

**Warranty**

**Information**

Warranty      Lifetime

---

***\*Product appearance and specifications are subject to change without notice.***

