

Single Bay USB 3.0 to SATA Hard Drive Docking Station, USB 3.0 (5 Gbps) Hard Drive Dock, External 2.5/3.5" SATA I/II/III HDD/SSD Docking Station, Top-Loading Hard Drive Bay

Product ID: SATDOCKU3S




The SATDOCKU3S USB 3.0 Hard Drive Docking Station delivers full, instant access to any 2.5in or 3.5in SATA (SATA, SATA II, SATA III) hard drive (HDD) or solid state drive (SSD), without having to mount the drive in a computer or install it in an external enclosure. Large capacity drives (tested with hard drives up to 16TB at 7200 RPM) can be used to greatly enhance your computer's storage/backup capabilities.

Connected to the host computer through a single USB 3.0 SuperSpeed 5Gbps or USB 2.0 connection, the hard drive docking station provides a convenient, plug-and-play storage solution that delivers instant access to the hard drive without requiring a reboot.

Double the value of this hard drive docking station, using a SATA to IDE hard drive adapter (SAT2IDEADP), which enables you to use any 2.5 or 3.5in IDE hard drive in a SATA hard drive dock slot.

To ensure compatibility with your computer system, the SATDOCKU3S supports all of the leading operating system platforms, including: Microsoft Windows, Apple OSX, Linux, and Google Chrome OS.

Certifications, Reports and Compatibility



Applications

- Data recovery specialists who need quick access to drives for imaging
- Backup data quickly to an external drive for archiving
- Technicians who test or benchmark multiple hard drives
- Take advantage of new laptops and desktops with USB 3.0 connectivity
- Upgrade from a USB 2.0 drive dock to faster USB 3.0

Features

- **HARD DRIVE DOCKING STATION:** This single-bay hard drive docking station enables access to a 2.5/3.5" SATA drive for file backup, imaging, and data transfer over USB 3.2 Gen 1 (5 Gbps)
- **DRIVE COMPATIBILITY:** Supports a 2.5/3.5" SATA HDD/SSD of any capacity; OS Independent; IDE (SAT2IDEADP), mSATA (SAT2MSAT25), & M.2 SATA (SAT32M225) adapters sold separately
- **PERFORMANCE:** Toolless Top-loading design enables quick hot-swapping of idle drives; Backwards compatible with previous SATA & USB versions; No software / drivers required
- **SPECS:** Single-Bay Hard Drive Dock; SATA I/II/III; USB 3.2 Gen 1 (5 Gbps) Host Connection; Top-Loading Drive Bay with Eject Button; Power and Activity LED Indicators; Includes USB 3.2 (5 Gbps) Type-A Cable and Universal Power Adapter
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this Single-Bay Hard Drive Dock is backed for 2 years, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	2 Years
Fan(s)	No
Interface	USB 3.2 Gen 1 (5Gbps)
Number of Drives	1
Drive Size	2.5in & 3.5in
Compatible Drive Types	SATA
Chipset ID	ASMedia - ASM225CM

Performance

Type and Rate	USB 3.0 - 5 Gbit/s
	USB 2.0 - 480 Mbit/s

UASP Support	No
Type and Rate	SATA III (6 Gbps)
Max Drive Capacity	Currently tested with hard drives up to 16TB at 7200 RPM
Insertion Rating	15,000 Cycles

Connector(s)

Drive Connectors	1 - SATA Data & Power Combo (7+15 pin)
Host Connectors	1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Indicators

LED Indicators	1 - Power and Activity (Solid - Power, Blinking - Activity)
----------------	---

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Output Voltage	12V DC
Output Current	2.5A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	30

Environmental

Operating Temperature	5C to 80 (41F to 176F)
Storage Temperature	-40C to 70C (-40F to 158F)
Humidity	8~80% RH

Physical Characteristics

Color	Black
Material	Plastic

Product Length	5.7 in [14.5 cm]
Product Width	3.7 in [9.3 cm]
Product Height	2.6 in [6.5 cm]
Weight of Product	13.8 oz [392 g]

Packaging Information

Package Quantity	1
Package Length	6.8 in [17.2 cm]
Package Width	6.4 in [16.3 cm]
Package Height	3.7 in [9.4 cm]
Shipping (Package) Weight	1.6 lb [0.7 kg]

What's in the Box

Included in Package	1 - USB 3.0 HDD Dock
	1 - USB 3.0 Cable
	1 - Universal Power Adapter (NA,EU,UK,ANZ)
	1 - Instruction Manual

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***

