

1U Server Rack Shelf - Universal Vented Rack Mount Cantilever Tray for 19" Network Equipment Rack & Cabinet - Durable Design - Weight Capacity 55lb/25kg - 20" Deep Shelf, Black

**Product ID:** SHELF-1U-20-FIXED-V



The SHELF-1U-20-FIXED-V lets you add 1U 20 inches (50.8 cm) deep shelf to any EIA-310 compliant 19-inch rack or cabinet. The shelf is vented to improve airflow and help lower temperatures in your rack.

Quality construction

The fixed-rack shelf can hold up to 55 lbs (25 kg) of equipment and is constructed using 2.0 mm SPCC commercial-grade cold-rolled steel for long-term durability and sturdiness. Accommodate your accessories or non-mountable devices for ease of access or connectivity to your equipment.

Maximize ventilation

The vented shelf plate improves the airflow helping to dissipate heat away from your equipment for extended and cooler operation.

Hardware included

Conveniently includes M6 square cage nuts and M6 screws to set it up in no time.

The SHELF-1U-20-FIXED-V is backed by a StarTech.com lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

## Applications

## Features

- **UNIVERSAL 19" FIT:** This 1U vented server rack mount shelf is designed to fit EIA-310 compliant 19in server racks and can accommodate an internal depth of 20in (50.8cm) for your data, IT, networking, or equipment from brands like APC, Dell, Lenovo and HPE
- **DURABLE DESIGN:** Constructed with 2.0 mm thick SPCC commercial cold-rolled steel, the sturdy front mounted cabinet shelf ensures durability and supports a total weight of 55 lbs (25 kg) making it the perfect rack shelf for any environment
- **MAXIMIZE VENTILATION:** The vented shelf plate on the cantilever rack shelf helps to improve airflow to effectively dissipate heat away from your equipment
- **EASY ACCESS:** The shelf can be used for modems, routers, Wi-Fi access points, and other IT/network/telco equipment that can't be mounted on a rack or to store and access frequently used tools and supplies
- **STARTECH.COM ADVANTAGE:** IT professionals' choice for over 30 years, this 1U vented server rack shelf is backed for life by StarTech.com, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	1U
Cable Management	No
Industry Standards	EIA/ECA-310-E

---

### Performance

Weight Capacity (Stationary)	55.1 lb [25 kg]
------------------------------	-----------------

---

### Physical Characteristics

Color	Black
Material	Steel
Internal Width	17.2 in [43.6 cm]
Internal Depth	20.0 in [50.8 cm]
Product Length	20.0 in [50.8 cm]
Product Width	19.0 in [48.3 cm]
Product Height	1.7 in [4.3 cm]

---

Weight of Product	7.7 lb [3.5 kg]
-------------------	-----------------

---

**Packaging Information**

Package Quantity	1
Package Length	22.2 in [56.3 cm]
Package Width	22.4 in [56.9 cm]
Package Height	4.8 in [12.3 cm]
Shipping (Package) Weight	10.3 lb [4.7 kg]

---

**What's in the Box**

Included in Package	1 - Shelf
	4 - Plastic Washers
	4 - M6 Cage Screws
	4 - M6 Square Cage Nuts
	1 - Quick-Start Guide

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

