

## SPDIF Digital Coaxial or Toslink Optical to Stereo RCA Audio Converter

Product ID: SPDIF2AA



The SPDIF2AA Toslink/Optical SPDIF to RCA Audio Converter lets you convert a 2-channel Digital Coaxial or Toslink/Optical SPDIF input signal into an RCA analog stereo output.

Perfect for home and professional audio applications, this SPDIF to RCA audio converter saves the cost of upgrading equipment for compatible connections, and offers separate Digital Coax and Toslink inputs for dual-function conversion. The small form factor design makes it suitable for installation into virtually any location, regardless of space constraints, while still providing a lossless audio signal. Plus, the digital coaxial or Toslink to RCA converter supports plug-and-play installation, saving you time and hassle.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Connect newer Blu-Ray, DVD Players and Game Consoles to two channel analog stereo receivers
- Convert or extend your digital audio input into an analog format, without signal or quality loss

### Features

- Accepts Digital Coax or Toslink digital audio input

- Outputs analog L/R RCA stereo analog audio
- Compact form factor
- Easy to install and use
- 24-bit S/PDIF incoming bit stream
- Supports 32, 44.1, 48 and 96 KHz sampling rates

**Hardware**

Warranty	2 Years
AV Input	Digital Coaxial
	Toslink
AV Output	RCA Audio

**Performance**

Audio Specifications	2 channel (stereo) supported 32, 44.1, 48 and 96 KHz Sampling rates
----------------------	--

**Connector(s)**

Connector A	1 - Toslink (SPDIF, Optical) 1 - Digital Coax Audio (RCA)
Connector B	1 - Stereo Audio (2 x RCA)

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.4 A
Output Voltage	5 DC
Output Current	2.0 A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	10

---

**Environmental**

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	10~85 % RH Non-Condensing

---

**Physical Characteristics**

Color	Black
Material	Steel
Product Length	2.0 in [5.2 cm]
Product Width	1.7 in [4.2 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	2.5 oz [70 g]

---

**Packaging Information**

Package Quantity	1
Package Length	5.6 in [14.4 cm]
Package Width	6.9 in [17.5 cm]
Package Height	1.6 in [4.1 cm]
Shipping (Package) Weight	10.1 oz [286.0 g]

---

**What's in the Box**

Included in Package	1 - SPDIF to RCA converter
	1 - universal power adapter (NA, EU, UK, ANZ)
	1 - instruction manual

---

**Warranty Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*