

3ft (1m) USB-C Charging Cable, Charge & Sync, 60W (3A) PD, USB 2.0 Laptop Charger Cable, USB-IF Certified - USB C Charging Cord

Product ID: USB2CC1M



This USB-C to USB-C cable lets you charge and sync your USB Type-C devices. It's also compatible with Thunderbolt 3 ports.

Connect your newer USB-C mobile devices, such as the Samsung Galaxy S8, S8+, Nexus 6P, and 5X phones, to your computer. The cable delivers up to a 3 amp charge, and supports data transfer speeds of up to 480Mbps.

With up to 3A of power output, this USB Type-C cable can also be used to power a USB-C laptop, such as your Apple MacBook or Chromebook Pixel. Simply connect your laptop to your USB-C wall charger.

Replace the cable that came with your device, or keep one as a spare while you're traveling, so that all of your devices will be ready to use whenever you need them while you're on the road.

The USB Type-C connector is smaller and easier to use than previous USB connectors. With a reversible design, you can plug it into your devices with either side facing up. Insert the cable the right way every time - no more frustration or port damage.

This USB-C cable has been certified with USB-IF (USB Implementers Forum) in order to meet all USB 2.0 specifications. This includes all environmental, electrical and mechanical standards set by USB compliance. This ensures a high-quality, reliable cable for all your USB-C devices.

Certifications, Reports and Compatibility



Applications

- Power your USB-C enabled laptops with a USB Type-C wall charger
- Charge your USB-C mobile devices with USB-C computer or wall charger
- Sync your USB-C devices with a USB-C computer

Features

- USB-IF Certified
- Connect more easily with reversible USB Type-C connectors, which can plug into your devices with either side facing up
- Thunderbolt 3 port compatible
- Guaranteed reliability with our lifetime warranty
- Please note that this USB 2.0 cable does not support any video; For connecting or extending USB-C Displays/Monitors we recommend our USB-C 3.0 cables (e.g. USB31CC1M)

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)

Power

Power Delivery	60W
----------------	-----

Physical Characteristics

Color	Black
Connector Style	Straight

Wire Gauge	22/30 AWG
Cable Length	3.3 ft [1 m]
Product Length	3.3 ft [1.0 m]
Product Width	0.2 in [6.0 mm]
Product Height	0.5 in [1.2 cm]
Weight of Product	1.3 oz [36.0 g]

Packaging Information

Package Quantity	1
Package Length	4.2 in [10.7 cm]
Package Width	4.8 in [12.2 cm]
Package Height	0.7 in [1.7 cm]
Shipping (Package) Weight	1.3 oz [38.0 g]

What's in the Box

Included in Package	1 - 1m (3ft) USB 2.0 USB-C Cable - M/M
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***