

15m USB 2.0 Active Cable with 4 Port Hub - TAA

Product ID: USB2EXT4P15M



The USB2EXT4P15M 15m Active USB 2.0 Extension Cable features an integrated 4-Port Hub that lets you connect up to 4 USB 2.0 devices while overcoming distance restrictions and power source limitations.

The active USB 2.0 extension cable ensures performance beyond the 5-meter length limits of standard USB cables. Perfect for applications where you need to extend the connection distance of your USB peripherals, enabling you to connect them up to 15-meters (50-feet) away from the host computer.

Plus, the cable allows you to maximize the number of devices connected to your computer by allowing you to connect up to 4 devices through a single connection. For added convenience, the cable comes with a 2A power adapter to provide power to your 4 connected USB devices.

The USB2EXT4P15M cable supports the full USB 2.0 bandwidth of 480 Mbps, and is backed by StarTech.com's 2-year Warranty.

Certifications, Reports and Compatibility



Applications

- Connect 4 USB 2.0 devices to your computer through a single cable

- Extend the distance of USB peripherals beyond the USB 2.0 5-meter limitation

Features

- High Speed USB 2.0 compliant, with supported data transfer rates up to 480 Mbps
- Backward compatible with USB 1.1/1.0 devices
- Includes a 2A external power adapter
- Overcurrent detection and protection for all 4 ports
- Plug and Play and Hot Swap compatible

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	4 - USB 2.0 Type-A (4 pin, 480Mbps)

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.5 A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	H
Power Consumption (In Watts)	10

Environmental

Operating Temperature	0C - 70C (32F - 158F)
Storage Temperature	-25C - 85C (13F - 185F)
Humidity	30-75% Room Humidity

Physical Characteristics

Color	Black
Wire Gauge	24 AWG
Cable Length	49.2 ft [15 m]
Product Length	49.2 ft [15.0 m]
Product Width	2.2 in [5.5 cm]
Product Height	1.4 in [3.5 cm]
Weight of Product	1.4 lb [0.6 kg]

Packaging Information

Package Quantity	1
Package Length	9.0 in [22.8 cm]
Package Width	8.4 in [21.4 cm]
Package Height	2.4 in [6.1 cm]
Shipping (Package) Weight	2.0 lb [0.9 kg]

What's in the Box

Included in Package	1 - 15m USB 2.0 Active Cable with 4 Port Hub 1 - Universal Power Adapter 1 - Plug Adapters for North America, UK, Europe, and Australia
---------------------	---

Warranty Information

Warranty	2 Years
----------	---------

***Product appearance and specifications are subject to change without notice.**