

USB to VGA Adapter, External USB Video Graphics Card for PC and MAC, 1920x1200, USB 2.0
Display Adapter - a direct replacement for USB32VGAPRO

Product ID: USB2VGAPRO2



The USB2VGAPRO2 USB to VGA Adapter functions as an external graphics card for Windows and Mac computers - the perfect solution for turning your desktop or laptop computer into a dual or multi-monitor environment, all through the simplicity and convenience of USB.

The USB-VGA Adapter delivers high quality video (up to 1920x1200) for a variety of applications and is capable of simultaneously running up to five additional displays from a single computer (using four USB2VGAPRO2 External Video Adapters). The adapter connects to a host computer through a USB 2.0 port, acting as an external VGA video card to either extend or mirror the desktop shown on the existing display - without having to open the computer case.

Featuring driver support for Microsoft Windows (including Aero themes) and Mac OS X, and with video support for resolutions up to 1920x1200, this USB-VGA video adapter is the ideal solution for a wide range of operating environments as well as large-screen displays/monitors.

The USB2VGAPRO2 USB to VGA Adapter is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility





Applications

- Add multiple (up to five) monitors / projectors to your computer setup using one USB2VGAPRO2 device for each additional display
- View large or multiple spreadsheets across multiple displays
- Increase productivity by running multiple applications on different VGA screens; check your email on one display while editing a document on the other
- Use the USB-VGA adapter to connect your PC to your television for showing family pictures and movies
- Connect multiple VGA monitors to a single computer to create engaging multimedia presentations
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- Optimal performance at 1920x1200 and ideal for use with 24" to 26" monitors or smaller
- Support for Aero themes in Windows
- Works with Mac OS X
- Connect up to five adapters to one PC for a true extended desktop experience
- USB-Powered operation, no external power adapter required
- Quick and easy installation
- Powered by DisplayLink DL-195 chip

Hardware

Warranty	2 Years
AV Input	USB 2.0
AV Output	VGA
USB Pass-Through	No
Memory	16MB

Chipset ID	DisplayLink - DL-195
<hr/>	
Performance	
Maximum Analog Resolutions	1920x1200 (32-bit Color)
Supported Resolutions	<p>Standard(16/32 bit):</p> <p>640x480, 800x600, 1024x768, 1280x1024, 1600x1200</p> <p>Widescreen(16/32 bit):</p> <p>1366x768, 1440x900, 1680x1050, 1920x1200</p>
MTBF	87,703 hours
<hr/>	
Connector(s)	
Connector Type(s)	<p>1 - USB 2.0 Type-A (4 pin, 480Mbps)</p> <p>1 - VGA (15 pin, High Density D-Sub)</p>
<hr/>	
Software	
OS Compatibility	<p>Windows XP (32-bit), Vista, 7, 8, 8.1, 10, 11, 11 ARM</p> <p>macOS 10.6 - 10.12, 10.14 - 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1</p> <p>Chrome OS v55+</p> <p>Ubuntu 14.04, 16.04, 18.04, 20.04, 22.04, 24.04</p>
<hr/>	
Special Notes / Requirements	
System and Cable Requirements	<p>System Processor: 1.2GHz</p> <p>System Memory: 512MB</p>
Note	<p>Power PC-based Macintosh computers, such as late-model iMacs, PowerBooks and PowerMacs, are not currently supported</p> <p>Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources</p> <p>This USB video adapter is not intended for graphical intensive applications, such as gaming</p>
<hr/>	
Indicators	
LED Indicators	1 - Blue - Power

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	10C to 40C (50F to 104F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	<85% non-condensing

Physical Characteristics

Color	Black
Cable Length	6.5 in [165 mm]
Product Length	3.1 in [78 mm]
Product Width	1.7 in [4.4 cm]
Product Height	0.6 in [1.6 cm]
Weight of Product	2.3 oz [64 g]

Packaging Information

Package Quantity	1
Package Length	5.7 in [14.5 cm]
Package Width	8.3 in [21.1 cm]
Package Height	1.6 in [4.0 cm]
Shipping (Package) Weight	6.9 oz [196.0 g]

What's in the Box

Included in Package	1 - USB to VGA Adapter
	1 - Instruction Manual

Warranty Information

Warranty	2 Years
----------	---------

***Product appearance and specifications are subject to change without notice.**