

1.6ft (50cm) USB-C Cable, USB 10Gbps, 60W (3A) Power Delivery, 8K 60Hz / 4K 144Hz DP Alt Mode - Thunderbolt Compatible

Product ID: USB31CC50CM



This USB-C to USB-C cable lets you connect a USB 3.2 Gen 2, USB Type-C device, such as a hard drive or mobile device, to the USB-C port on your computer, charger or tablet. The cable is also compatible with Thunderbolt 3 ports.

This 0.5-meter cable is great for close-range connections to charge and sync your mobile devices with your laptop. Moving large files or transferring movies can be done in seconds, at twice the speed of USB 3.2 Gen 1 and 20x faster than USB 2.0 -- all while charging your device with 60 watts (3 amps) power delivery.

You can also use the cable to charge your devices from a USB-C wall charger, car charger or power bank -- perfect for people on the move, for providing simple, tidy connections.

The short cable lets you set up in small offsite workspaces, or in a coffee shop or hotel room. It lets you connect a USB 3.2 Gen 2 peripheral device, such as your external hard drive to your laptop, without excess cable getting in your way.

With a bandwidth of 10Gbps, this USB 3.2 Gen 2 cable lets you sync your USB Type-C devices in no time at all. You can spend less time transferring and backing up your data and more time focusing on your projects and presentations.

The cable supports full 4K 60Hz video and DisplayPort 1.2 and is compatible with existing DisplayPort displays. It's ideal for connecting your docking station or laptop to a monitor with astonishing resolution, contrast, and color depth, for amazing detail.

Certifications, Reports and Compatibility



Applications

- Connect a USB 3.1 device such as a portable hard drive or docking station to a USB-C laptop or desktop computer
- Charge and sync your USB-C mobile digital devices with your computer
- Charge your USB-C devices with a wall charger, car charger or power bank

Features

- Short 50 cm cable perfect for close-range connections and portable applications
- Download movies, back up your files, and sync your mobile devices faster with data transfer rates up to 10Gbps (USB 3.2 Gen 2)
- Thunderbolt 3 port compatible
- Supports full 4K 60Hz video and DisplayPort 1.2
- Guaranteed reliability with our 2-year warranty

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	4K @ 60Hz
Type and Rate	USB 3.2 Gen 2 - 10 Gbit/s

Connector(s)

Connector A	1 - USB 3.2 Type-C (24 pin, Gen 2, 10Gbps)
Connector B	1 - USB 3.2 Type-C (24 pin, Gen 2, 10Gbps)

Power

Power Delivery	60W
----------------	-----

Environmental

Operating Temperature	0C to 50C (32F to 122F), 15-85% RH (Non-Condensing)
Storage Temperature	-25C to 85C (-13F to 185F), 15-85% RH (Non-Condensing)
Humidity	5% to 90 % RH (no condensation)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	26/32 AWG
Cable Length	1.6 ft [0.5 m]
Product Length	19.7 in [50.0 cm]
Product Width	0.5 in [1.2 cm]
Product Height	0.3 in [6.5 mm]
Weight of Product	0.8 oz [24.0 g]

Packaging Information

Package Quantity	1
Package Length	5.1 in [13.0 cm]
Package Width	4.8 in [12.3 cm]
Package Height	0.6 in [1.4 cm]
Shipping (Package) Weight	1.1 oz [30.0 g]

What's in the Box

Included in Package	1 - USB-C cable
---------------------	-----------------

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*