

6 ft SuperSpeed USB 3.0 (5Gbps) Cable A to B - M/M

**Product ID:** USB3SAB6



StarTech.com's 6ft USB 3.2 Gen 1 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.2 Gen 1 standard.

Designed for next-generation SuperSpeed USB device connections, the 6ft USB 3.2 Gen 1 cable offers a throughput of up to 5Gbps when used with a USB 3.2 Gen 1 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 6ft USB 3.2 Gen 1 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 6ft USB 3.2 Gen 1 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

## Certifications, Reports and Compatibility



## Applications

- Superspeed 3.0 data transfer with USB 3.0 compliant devices

## Features

- Cable and Connectors our compliant with USB 3.2 Gen1 SuperSpeed specifications

---

**Hardware**

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Foil shielded twisted pair

---

**Performance**

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

---

**Connector(s)**

Connector A	1 - USB Type-A (9 pin, 5 Gbps)
Connector B	1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)

---

**Environmental**

Operating Temperature	-10C to 55C (14F to 131F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	20%-80% RH (non-condensing)

---

**Physical Characteristics**

Color	Blue
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	2.4 oz [68.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	5.6 in [14.2 cm]
Package Width	7.8 in [19.8 cm]
Package Height	0.8 in [2.1 cm]

Shipping (Package) 2.8 oz [80.0 g]  
Weight

---

**What's in the Box**

Included in Package 1 - 6 ft SuperSpeed USB 3.0 Cable A to B - M/M

---

**Warranty  
Information**

Warranty Lifetime

---

*\*Product appearance and specifications are subject to change without notice.*

