

## 4-Port USB Wall Charger - International Travel - 34W/6.8A - White

**Product ID:** USB4PACWH



This 4-port charger lets you keep all of your mobile devices charged and ready to use, regardless of where you're located. Whether you're at home, in the office or travelling overseas, you can charge up to four devices at once.

The wall charger includes a universal power adapter, which lets you plug into any electrical socket almost anywhere in the world. No matter where you're travelling to, you can rest assured that you can keep your mobile devices charged and ready to use.

Plus, its compact design makes this charger the perfect mobile accessory for storing in your carry-on luggage. The portable USB wall charger features a folding North American plug that tucks away nicely to fit inside your laptop bag or other carrying case. And, you can easily throw in the correct international plug for wherever you're going, so that you're all set to charge your device when you arrive at your destination.

The multi-port charger features Smart IC technology, which enables it to identify what type of device is connected to each port. By recognizing the attached device, the charger delivers the optimal charge specific to each device.

Plus, the charger can deliver 34 watts of power in total, sharing 6.8 amps of power between all four ports. This means you can charge two tablets and two phones at the same time.

The charger supports USB Battery Charging Specification 1.2, which ensures compatibility with a broad range of mobile devices, including the Apple iPhone and iPad, the Microsoft Surface tablet, the Samsung Galaxy Tab, Nexus phones and more.

Keep the charger at your desk and use it as a dedicated charging station for your mobile devices, at home or in the office. Consolidating your USB devices onto a single multi-port USB charger offers a more efficient solution and saves space because you don't need to use multiple wall outlets or power bars.

The USB charging station features built-in safety measures to ensure that all of your devices are protected against damage from overheating, overvoltage, overcurrent or short circuiting. If the 34-watt limit is exceeded, the power being sent to the connected devices will turn off and the charger will reset itself until the load is reduced to safe levels.

The USB4PACWH is backed by our 2-year warranty to ensure dependable performance.

Note: Some mobile devices, such as certain Samsung and BlackBerry devices, use proprietary power connections which are not compatible with aftermarket chargers. Please consult the manufacturer's documentation to ensure compatibility with the USB4PACWH.

## Certifications, Reports and Compatibility



## Applications

- Charge two tablets and two phones simultaneously
- Charge four phones at once
- Set up a dedicated charging station for your home or office

## Features

- Charge your devices at home or overseas with the included universal power adapter
- Deliver the fastest possible power output required for each connected device - up to a total of 34 watts (6.8 amps) shared between all four ports
- Charge almost any mobile device that supports USB Battery Charging Specification 1.2 support

---

### Connector(s)

Warranty	2 Years
Connector A	1 - NEMA 1-15 Power (North America) 1 - BS 1363 Power (UK) 1 - CEE 7/16 Power (Europlug) 1 - AS/NZS 3112 Power (Australia)
Connector B	4 - USB 2.0 Type-A (4 pin, 480Mbps)

---

### Power

Input Voltage	100 - 240 AC
Input Current	0.9A

Output Voltage 5 DC

Output Current 6.8A

---

**Physical Characteristics**

Color White

Product Length 2.3 in [5.9 cm]

Product Width 2.1 in [5.3 cm]

Product Height 1.7 in [4.3 cm]

Weight of Product 7.4 oz [210.0 g]

---

**Packaging Information**

Package Quantity 1

Package Length 8.3 in [21.2 cm]

Package Width 3.2 in [8.1 cm]

Package Height 2.2 in [5.5 cm]

Shipping (Package) Weight 8.9 oz [252.0 g]

---

**What's in the Box**

Included in Package 1 - 4-port USB wall charger

1 - Universal Power Adapter (NA/UK/EU/AUS)

---

**Warranty Information**

Warranty 2 Years

---

*\*Product appearance and specifications are subject to change without notice.*