

USB C to Quad HDMI Adapter, USB-C to 4x HDMI Monitor Converter for Windows (no support for macOS/ChromeOS/Linux) - TAA

Product ID: USBC2HD4



This USB C to HDMI adapter lets you extend your desktop by adding four independent HDMI monitors or displays to your computer using a single USB Type-C port.

This USB-C to 4 HDMI adapter features four video outputs, boosting your productivity by giving you more screen space to work from. With multiple displays you have the freedom to access multiple applications at the same time and reference material on one display while you compose on the other. Use the USBC to HDMI multi-monitor adapter to extend or mirror your displays.

This quad monitor adapter lets you harness the video capabilities from your computer or laptop's USB-C connection, to deliver high-definition resolutions up to 1920x1080 (1080p) on all four ports. The adapter also supports 2-channel audio through HDMI.


The USB Type-C to HDMI display adapter converter is equipped with a 1.6 ft. (0.5 m) attached USB-C cable that provides added distance between the adapter and your host device, ensuring a flexible setup. It also supports an automatic driver installation for ease of use.

The external video adapter is bus-powered, with no external power required.

The Multi-Monitor Assistant application provides a user interface that assists users with multitasking, and allows you to quickly switch from monitor to monitor. It enables additional features, assisting users with dragging and dropping, optional zooming, split scaling and cascading windows to the main display.

Note:

Certifications, Reports and Compatibility



Applications

- Add up to four displays to your workstation
- Run multiple applications on different screens
- Mirror your primary display onto a HDTV

Features

- **COMPATIBILITY:** This adapter is only compatible with Windows and does not support macOS, ChromeOS or Linux; Works with all Windows X86/X64/ARM platforms: Intel, AMD, and Snapdragon X Copilot+ PC; Administrator rights are required to install the drivers
- **QUAD MONITOR DISPLAY ADAPTER:** USB 3.0 to 4x HDMI video adapter lets you extend your desktop by adding up to four HDMI monitors to your laptop or desktop computer; 4x 1080p 60Hz displays; 2ch audio (one source replicated to all displays through HDMI)
- **INCREASE PRODUCTIVITY:** USB 3.0 to HDMI adapter supports a total of 5 displays in extended mode (incl. laptop screen) at your workstation or working remotely from home; External video graphics card is USB bus-powered with no extra power supply required
- **MULTI-MONITOR ASSISTANT:** Increase productivity w/ included software for multi-tasking and window arrangement; drag & drop windows to a selected monitor, zoom in/out, and split/scale
- **EASY SETUP:** USB-A to HDMI quad monitor adapter dongle is equipped w/ a 1.6ft (50cm) attached USB-A cable for added distance between the adapter & host device for multiple monitor workspace or HDTV boardroom setup

Hardware

Warranty	3 Years
AV Input	USB-C
AV Output	HDMI
Chipset ID	Trigger T6-688SL IT66122

Performance

	Supported Resolutions	1920x1080 (1080p) / 60Hz
	Audio Specifications	HDMI - 2 Channel Audio
Connector(s)		
	Connector A	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)
	Connector B	4 - HDMI
Software		
	OS Compatibility	Windows 11, 11 ARM, 10
Special Notes / Requirements		
	Note	This USB video adapter is not intended for graphical-intensive applications, such as CAD or gaming
Environmental		
	Operating Temperature	0C to 45C (32F to 113F)
	Storage Temperature	-10C to 75C (14F to 167F)
	Humidity	< 85% non-condensing
Physical Characteristics		
	Color	Space Gray
	Material	Aluminum
	Cable Length	1.6 ft [0.5 m]
	Product Length	4.0 in [10.1 cm]
	Product Width	3.2 in [8.0 cm]
	Product Height	0.6 in [1.6 cm]
	Weight of Product	5.8 oz [165.0 g]
Packaging Information		
	Package Quantity	1
	Package Length	8.4 in [21.3 cm]
	Package Width	5.7 in [14.4 cm]

Package Height	1.7 in [4.2 cm]
Shipping (Package) Weight	9.5 oz [268.0 g]

What's in the Box

Included in Package	1 - USB-C to HDMI Adapter
	1 - Quick-Start Guide

Warranty Information

Warranty	3 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***