

Datamate L-Tek Connectors

Female Cable Assemblies

- Ready-made cable assemblies, fully tested and inspected.
- Constructed with Contact 1 to Contact 1, Contact 2 to Contact 2, etc.
- Double Row connectors (10 contacts and larger) compatible with plastic Hood shown on following page.
- For multicolor sequence, check applicable Technical Drawing.



SINGLE ROW, SINGLE ENDED	DOUBLE ROW, SINGLE ENDED														
FEMALE - FEMALE DOUBLE ENDED															
HOW TO ORDER															
TERMINATION - SECOND END <table border="1"> <tr> <td>L</td><td>Loose cut end</td></tr> <tr> <td>F</td><td>Female connector</td></tr> </table>	L	Loose cut end	F	Female connector	CABLE LENGTH <table border="1"> <tr> <td>0150</td><td>150mm</td></tr> <tr> <td>XXXX</td><td>XXXXmm</td></tr> </table>	0150	150mm	XXXX	XXXXmm						
L	Loose cut end														
F	Female connector														
0150	150mm														
XXXX	XXXXmm														
CABLE SIZE <table border="1"> <tr> <td>1</td><td>22 AWG</td></tr> <tr> <td>2</td><td>24 AWG</td></tr> <tr> <td>3</td><td>26 AWG</td></tr> <tr> <td>4</td><td>28 AWG</td></tr> <tr> <td>5</td><td>30 AWG</td></tr> </table>	1	22 AWG	2	24 AWG	3	26 AWG	4	28 AWG	5	30 AWG	WIRE COLOR <table border="1"> <tr> <td>05</td><td>White cable (double-ended)</td></tr> <tr> <td>68</td><td>Multicolor cable (single-ended)</td></tr> </table>	05	White cable (double-ended)	68	Multicolor cable (single-ended)
1	22 AWG														
2	24 AWG														
3	26 AWG														
4	28 AWG														
5	30 AWG														
05	White cable (double-ended)														
68	Multicolor cable (single-ended)														
TOTAL NO. OF CONTACTS <table border="1"> <tr> <td>02 to 07, 17</td><td>Single Row</td></tr> <tr> <td>04, 06, 08, 10, 12, 14, 16, 18, 20, 26, 34</td><td>Double Row</td></tr> </table>	02 to 07, 17	Single Row	04, 06, 08, 10, 12, 14, 16, 18, 20, 26, 34	Double Row											
02 to 07, 17	Single Row														
04, 06, 08, 10, 12, 14, 16, 18, 20, 26, 34	Double Row														

All dimensions in mm.