







RECOMMENDED LAND PATTERN DIMENSION OF PCB
RECOMMENDED METAL MASK THICKNESS: 0.15mm



SIGNAL PORTION CROSS SECTION (10 : 1)




GROUND PORTION CROSS SECTION (10 : 1)



- NOTES
- 6 HATCHED  PARTS: GROUND CIRCUIT.
 - SMT LEAD-COPLANARITY: 0.1 MAX.
 - THIS PRODUCT HAS NO POLARITY TO PATTERN FOR MOUNTING.
 - MAKE SURE WIDTH OF PATTERN IS WITHIN THAT OF LAND. OR LEAD MAY TOUCH PATTERN. (THIS APPLIES TO HATCHED  AREA.)
 - DO NOT MOUNT OTHER DEVICES ONTO  AREA. OR MATING PAIR CANNOT BE MATED.
 - TO BE EMBOSSED CARRIER TAPED AS SPECIFIED IN SHEET 2.
 - THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.


3, 4	PHOSPHOR BRONZE	TIN PLATING							
		CONTACT AREA : GOLD 0.1μm min.							
2	COPPER ALLOY	LEAD AREA : GOLD FLASH	7	POLYIMIDE	(TAPE FOR VACUUM PICKUP)				
		UNDER PLATING : NICKEL 1μm min.	6	PET	TOP COVER TAPE				
1	LCP	BEIGE UL94V-0	5	PS	EMBOSSED CARRIER TAPE				
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS				
UNITS mm		SCALE 5 : 1	COUNT 	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE	
 HIROSE ELECTRIC CO., LTD.		APPROVED : HS. OKAWA	13. 08. 07	DRAWING NO.	EDC3-152601-02				
		CHECKED : HT. YAMAGUCHI	13. 08. 07	PART NO.	FX11B-60P/6-SV(92)				
		DESIGNED : TY. EDAGAWA	13. 08. 07	CODE NO.	CL573-0512-3-92				
		DRAWN : TY. EDAGAWA	13. 08. 07						

DRAWING FOR PACKING(2:1)




THE DIRECTION OF PULLING OUT →


A (5 : 1)



DETAIL FOR VACUUM PICKUP (5:1)



REELED DIMENSION(Free)



- NOTES
- 1 REEL : 1000 CONNECTORS.
 - 2 MINIMUM 10 COMPARTMENTS FROM BOTH REEL ENDS REMAIN EMPTY.
 - 3 THIS PRODUCT HAS NO POLARITY TO TAPE AND REEL PACKAGING.
 - 4 THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
 - 5 REMOVE THE VACUUM PICKUP TAPE AFTER MOUNTING THE CONNECTOR.

HRS

DRAWING NO.	EDC3-152601-02
PART NO.	FX11B-60P/6-SV(92)
CODE NO.	CL573-0512-3-92

2/2