

LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			F	OBSOLESCENCE OF 163179-1	02JAN2013	KJK	RP

NOTE

① OBSOLETE

14	131419-2	PARTITION	—	21
1	132526-1	CASE	—	20
5	163179-1	.250 SRS LINE SPLICE CONN. (WHITE)	—	19
10	9-160463-2	1,0-2,5mm ² .250 SRS PIDG PIGGY-BACK FASTON		18
10	9-160313-2	1,0-2,5mm ² .250 SRS PIDG FATON REC.	—	17
10	165034-0	2,7-6,6mm ² PIDG RINGTONGUE	1/4	16
10	130171-0	2,7-6,6mm ² PIDG RINGTONGUE	M5	15
10	35108-0	2,7-6,6mm ² PIDG RINGTONGUE	M4	14
20	320862-0	0,25-1,6mm ² FLANGED SPADE	M4	13
20	130094-0	0,25-1,6mm ² PIDG RINGTONGUE	M5	12
20	320565-0	0,25-1,6mm ² PIDG RINGTONGUE	M4	11
20	320619-0	0,25-1,6mm ² PIDG RINGTONGUE	M3,5	10
20	165142-0	0,25-1,6mm ² PIDG SPADE	—	9
20	35559-0	1,0-2,6mm ² PIDG SPADE	M3,5	8
20	326861-0	0,25-1,6mm ² PIDG SPADE	M2,6	7
20	31890-0	0,25-1,6mm ² PIDG RINGTONGUE	M4	6
20	36150-0	0,25-1,6mm ² PIDG RINGTONGUE	M3,5	5
20	31880-0	0,25-1,6mm ² PIDG RINGTONGUE	M2,6	4
10	34072-0	2,7-6,6mm ² P.G. BUTT-SPLICE	—	3
15	34071-0	1,0-2,6mm ² P.G. BUTT-SPLICE	—	2
20	34070-0	0,25-1,6mm ² P.G. BUTT-SPLICE	—	1
QTY	NUMBER	NAME	STUD SIZE	ITEM


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - F



DIMENSIONS: mm		DWN J.v.LIEMPT 01 AUG 1996	MATERIAL —		FINISH —		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		CHK A. BIJNEN 02 MAR 01	 TE Connectivity				
		APVD A. BIJNEN 02 MAR 01					
		PRODUCT SPEC —		NAME P.I.D.G. INTRODUCTION ASSORTIMENT			
		APPLICATION SPEC —					
WEIGHT —		SIZE A4	CAGE CODE 00779	DRAWING NO C-165346	RESTRICTED TO —		
		CUSTOMER DRAWING			SCALE —	SHEET 1 OF 1	REV F