

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2005

© COPYRIGHT 2005

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

A1

-

P

LTR

DESCRIPTION

DATE

DWN


APVD

CERTILOK DIE SET FOR FASTON 6.3 mm - WIRE RANGE 0,32-0,75 mm²
Certilok-Matrize fuer Faston 6.3 mm - Querschnittsbereich 0,32-0,75 mm²

Matrize in Kombination mit Certilok Basishandzange TE PN 169400 verwenden
Die set used in combination with Certilok basis hand tool TE PN 169400

Lieferumfang: Matrize mit Kontaktpositionierer TE PN 9-1579013-7 und Bedienungsanleitung 411-18465
Shipment: Die set with contact locator TE PN 9-1579013-7 and instruction sheet 411-18465

Kontaktpositionierer als Ersatzteil erhaeltlich (Siehe Zeichnung TE PN 9-1579013-7)
Contact locator available as spare part (see drawing TE PN 9-1579013-7)




Kontakt	DGB (mm ²)	Drahtcrimp / Wire Crimp		Isolationscrimp/Insulationcrimp		Isol.Ø	Betriebsanl.
Contact	Wire Range	Hoehe/Height mm	Breite/Width mm	Hoehe/Height mm	Breite/Width mm	Ins.Range	Instr.Sheet
41968 41969 140794 160412 181902	0,32	1,24 ±0,05	2,29 F	-----	3,30 F	1,1-1,4	411-18465
	0,50	1,30 ±0,05		-----		1,4-1,6	
	0,75	1,38 ±0,05		-----		1,7-1,9	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm



MATERIAL 1.2767

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±°

FINISH 48-52 HRC

DWN Ch.Witt 29JUN2007

CHK -

APVD -

PRODUCT SPEC

APPLICATION SPEC

WEIGHT 90 g

CUSTOMER DRAWING

tyco
Electronicstyco Electronics AMP GmbH
D - 64625 Bensheim

NAME

DIE SET FOR FASTON 6.3
(0.32-0,75 mm²)

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-9-1579022-1 -

SCALE 2:1

SHEET 1 OF 1

REV A