




REVISIONS				
ZONE	LTR	ECN	DESCRIPTION	DATE
	H	25932	REVISED & REDRAWN. ORIGINAL RE-LEASE BY 11-15-69 KAM R. CHESS	7-1-81
	J	40497	UPDATE REV LETTER	9/1/00

QTY	PART NO.	DESCRIPTION	MAT'L AND SPEC.	ITEM NO.
1	003-1386-0001	RECEPT. SUBASSY, BNC UG-909/U		3
1	003-0765-0001	WASHER	BRASS PER QQ-B-626	2
1	003-0484-0000	HOUSING	BRASS PER QQ-B-626	
1	003-0187-0000	FERRULE	BRASS PER QQ-B-626	
1	003-0676-0000	NUT	BRASS PER QQ-B-626	
1	003-0490-0001	HOUSING SUBASSY		
1	003-0372-0002	CONTACT, SOCKET	BERYLLIUM COPPER, QQ-C-530	
1	003-0373-0001	INSULATOR	TEFLON PER L-P-403	
1	003-0481-0001	INSULATOR	TEFLON PER L-P-403	
1	003-0491-0002	CONTACT, PIN	BRASS PER QQ-B-626	
1	003-1455-0001	ADAPTER SUBASSY, S-93 PLUG		1

NOTES: UNLESS OTHERWISE SPECIFIED:
1. END B MATES WITH ALL 93 SERIES SCREW TYPE JACKS AND RECEPTACLES.
2. END A MATES WITH ALL BNC SERIES PLUGS.
3. SILVER PLATE .0002 MIN PER QQ-S-365, TYPE II, GRADE A.
4. GOLD PLATE PER MIL-G-45204, TYPE II, GRADE C, CLASS I.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± ± .XXX ±		CONTRACT NO.		APPROVALS		DATE	
MATERIAL		DRAWN HENNYC		CHECKED Etkan		7/1/81	
FINISH		PR. ENG. H. Gutierrez		APPROVED		7/1/81	
NEXT ASSY		USED ON		APPROVED		7/1/81	
APPLICATION		DO NOT SCALE DRAWING		These drawings and specifications are the property of Microdot Inc., are issued in strict confidence and shall not be divulged, be reproduced or copied, or used as the basis for the manufacture or sale of any article without written permission of Microdot Inc.		SCALE	
				SIZE B		CODE IDENT NO. 98278	
				DRAWING NO. 033-0129-0001		SHEET OF	

**MALCO**
A MICRODOT COMPANY, INC.
306 PASADENA AVE., SO. PASADENA, CALIF. 91030

ADAPTER
BNC BULKHEAD RECEPTACLE
TO S-93 PLUG

PROD. CODE 931
CODE CDM