





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASED	10JAN2024	AK	HT
	A1	REVISED PER ECN-24-295269	25NOV2024	A.K	H.T




- 1 HOUSING, INSERTS AND CONTACT OVERMOLDS: LCP, BLACK.
CONTACTS: COPPER ALLOY.
SOLDER WASHERS: NICKEL SILVER.
- 2 CONTACTS: 0.76µm GOLD ON MATING INTERFACE.
TIN PLATED ON PCB TAILS.
3. MINIMUM PC BOARD THICKNESS:
SINGLE SIDED = 1.57 MIN
DOUBLE SIDED = 2.2 MIN
- 4 DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- 5 PART NUMBER AND DATE CODE MARKED IN APPROXIMATE
AREA SHOWN.
- 6 RECOMMENDED COMPONENT, TRACES AND SOLDER MASK
KEEP OUT AREA. SURFACE SUITABLE FOR SOLDER.





SCALE 3:1


GLUE PAD	2394949-2
METAL PINS	2394949-1
HOLD DOWNS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02AUG2021 C. VALENTINE CHK 02AUG2021 E. BRIANT APVD 02AUG2021 E. BRIANT		 TE Connectivity													
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE CONNECTOR, 76 P QSFP 112 STACKED													
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-160505		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO					
MATERIAL		FINISH		APPLICATION SPEC 114-78076/78077		A2		00779		C=2394949		-					
				WEIGHT 8.9g		CUSTOMER DRAWING						SCALE 4:1		SHEET 1 OF 3		REV A1	

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTINE 02AUG2021	TE Connectivity			
DIMENSIONS: mm		CHK E. BRIANT 02AUG2021				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD E. BRIANT 02AUG2021	NAME RECEPTACLE CONNECTOR, 76 P QSFP 112 STACKED			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-160505	SIZE A2			
MATERIAL		APPLICATION SPEC 114-78076/78077	CAGE CODE 00779		DRAWING NO C-2394949	
FINISH		WEIGHT 8.9g	RESTRICTED TO -		SCALE 4:1	
		CUSTOMER DRAWING	SHEET 2 OF 3		REV A1	



© 2020 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



PACKAGING QUANTITY

P/N	INNER	MIDDLE	OUTER
2394949-1	24 PCS/TRAY	48 PCS/INNER BOX	192 PCS/BOX

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTINE CHK E. BRIANT APVD E. BRIANT	02AUG2021 02AUG2021 02AUG2021	TE Connectivity		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE CONNECTOR, 76 P QSFP 112 STACKED		
MATERIAL		FINISH		PRODUCT SPEC 108-160505	SIZE A2	RESTRICTED TO -
				APPLICATION SPEC 114-78076/78077	CAGE CODE 00779	
				WEIGHT 8.9g	DRAWING NO C-2394949	
				CUSTOMER DRAWING	SCALE 1:1	SHEET 3 OF 3
						REV A1