




P	LTR	DESCRIPTION	DATE	DWN	APVD
NC		NEW RELEASE PER E.O. PI8277	09MAR2003	-	RDR
A		REVISED PER PCN E-20-013840	18SEP2020	MK	IG
B		REVISED PER PCN-24-219306	29AUG2024	CO	CB
C		REVISED PER PCN-25-233228	18DEC2024	RK	CB




8 DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY .
YEAR: FIRST AND SECOND DIGITS. (14=2014)
MONTH: THIRD DIGIT, EXCLUDING 1.A=JAN., B=FEB., C=MARCH...(K=OCT.)
DAY: FOURTH AND FIFTH DIGIT (14=14th DAY)
HOUR: SIXTH AND SEVENTH DIGIT (11=11AM)


7. THIS RECEPTACLE TO BE USED WITH 2411-002-1805 (PLASTIC) PANEL NUT.
6. FOR PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-021-0000.
5. THIS RECEPTACLE MATES WITH HDP26-18-***P/S*-***** (***** = ALL MODIFICATIONS)
4. FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DWG. 0425-015-0000.
3. RECOMMENDED PANEL THICKNESS: .062[1.57] TO .1875[4.76] MAX.
2. BACKSHELL ADAPTER COLOR REFLECTS WIRE SEAL DIAMETER. (GREEN="N" SEAL; GREY='T' SEAL; BLUE='E' SEAL).
1. FOR CONTACTS ARRANGEMENTS, SEE ENVELOPE DRAWING 0425-013-1800.

1.442±.010
[36.63±0.25]

Ø 1.507±.005
[38.28±0.12]



RECOMMENDED PANEL MOUNTING HOLE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. ROLINSKI 12AUG2003	 TE Connectivity		
		CHK J. APOSTOL 02SEP2003			
DIMENSIONS: INCH [MM]		APVD S. BEARD 18AUG2003	NAME PLASTI RECEPTACLE CONNECTOR BAYONET COUPLING HDP SERIES -L017 MOD		
		PRODUCT SPEC 108-151015	SIZE A3		
		APPLICATION SPEC 114-151015			
MATERIAL -		WEIGHT 23.1 g	CAGE CODE 00779	DRAWING NO G-HDP24-18-XPSX-L017	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 2.000	SHEET 1 OF 1	REV C