

**Standard***Image for illustrative purpose only*

## Summary

[Request a quote](#)**Coax triax mixed en**

Nb of contacts Coax	1
Size	0E
Series	E - Outdoor Stepped Insert

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/gba-0e-250-fn.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/gba-0e-250-fn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Nb of contacts Coax	1
Rated current	6 A
Impedance	50 Ohms
Cable type	RG 178 B/U, RG 196 A/U, RG 188 A/U, RG 316 B/U, RG 174 A/U, HF-2114, RG 122 /U


## Form & Material

Shell style / Model id	GBA - Locking washer
Housing material	Bronze (nickel plated [SAE AMS QQ N 290]) washer
Keying	No keying
Weight	0.76 g

## Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	No IP rating
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]

## Drawings



No keying

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/gba-0e-250-fn.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/gba-0e-250-fn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Dimensions

	<b>A</b>	<b>C</b>	<b>L</b>
mm.	19.6	14.1	1.2
in.	0.77	0.56	0.05

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/gba-0e-250-fn.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/gba-0e-250-fn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.