



DO NOT
SCALE FROM
THIS PRINT



ASP-239731-XX

- PART NUMBER
- 01: -03.5 LEAD STYLE, MATTE TIN TAILS, -A PINS
 - 02: -03.5 LEAD STYLE, MATTE TIN TAILS, NO -A PINS
 - 03: -03.5 LEAD STYLE, TIN/LEAD TAILS, -A PINS
 - 04: -03.5 LEAD STYLE, TIN/LEAD TAILS, NO -A PINS




NOTES:


1. VITA 93 STANDARD PART SET UP AS ASP.
2. APPLIES TO PART NUMBERS -01 & *-03 ONLY.
3. PARTS TO BE PACKAGED IN TAPE & REEL
4. ORDERS WILL BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM.
5. -0 COLUMN TERMINATION CONNECTORS ARE SOLDERED WITH OPTIMIZED SOLDER PASTE VOLUME IN PLACE OF AN ATTACHED SOLDER BALL, USING OVERSIZED RECTANGULAR STENCIL APERTURES CENTERED OVER ROUND PCB PADS (DESIGN VERIFIED THROUGH TESTING). THE PASTE COALESCE DURING REFLOW TO FORM A COLUMNAR SOLDER JOINT. FOR MORE INFORMATION, CONTACT SAMTEC'S INTERCONNECT PROCESSING GROUP (IPG@SAMTEC.COM).
6. K-DOT PAD INCLUDED, NOT SHOWN FOR CLARITY.

PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.	
DO NOT SCALE DRAWING SHEET SCALE: 4:1 INSULATOR: LCP, COLOR BLACK CONTACT: COPPER ALLOY PLATING: CONTACT AREA: .000030" GOLD REMAINDER: -01, -02: .000200" TIN *-03, *-04: .000200" TIN/LEAD (90/10)	
DESCRIPTION: VITA 93 ADM6 ASSEMBLY	
DWG. NO. ASP-239731-XX	
BY: J. BROWNING 02/05/2025 SHEET 1 OF 3	

REVISION C



RECOMMENDED PCB LAYOUT
ALL DIMENSIONS SYMMETRIC ABOUT THE CENTERLINE



RECOMMENDED STENCIL LAYOUT
STENCIL TO BE 0.127 [.0050] THICK

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

samtec
520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DO NOT SCALE DRAWING

SHEET SCALE: 6:1


DESCRIPTION: VITA 93 ADM6 ASSEMBLY

DWG. NO. ASP-239731-XX


BY: J. BROWNING 02/05/2025 SHEET 2 OF 3

TABLE 1			
PART No	LEAD STYLE	TAIL PLATING	-A PIN
ASP-239731-01	-03.5	TIN	YES
ASP-239731-02		TIN	NO
ASP-239731-03		TIN/LEAD	YES
ASP-239731-04		TIN/LEAD	NO

TABLE 2	
MATING PART No	B2B STACK HEIGHT (mm)
ASP-246148-XX	7
ASP-239729-XX	11



USER DIRECTION OF UN-REELING
POCKET NOT DETAILED



PACKAGING VIEW

• PROPRIETARY NOTE • THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.		
	520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code 55322	
	DESCRIPTION: VITA 93 ADM6 ASSEMBLY	
	DWG. NO. ASP-239731-XX	
DO NOT SCALE DRAWING	BY: J. BROWNING 02/05/2025	
SHEET SCALE: 2:1	SHEET 3 OF 3	