

CB 365/7,5 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

Version	Cable ties, 7.5 x 365 mm, Polyamide 66, 540 N
Order No.	1697940000
Type	CB 365/7,5 BK
GTIN (EAN)	4008190883010
Qty.	100 pc(s).

CB 365/7,5 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.25 mm	Depth (inches)	0.01 inch
Height	365 mm	Height (inches)	14.37 inch
Width	7.5 mm	Width (inches)	0.295 inch
Net weight	4.7 g		

Temperatures

Operating temperature range	-40...85 °C
-----------------------------	-------------

Installation materials

Bundle diameter, max.	100 mm	Bundle diameter, min.	8 mm
Cable diameter, max.	100 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	540 N	Tensile strength (Pound-force)	121 lbf
UL 94 flammability rating	V-2	UV-resistant	No

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02
ECLASS 13.0	27-14-07-02	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319262/-T1z1mm-S800/
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E317499

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Approval/Certificate/Document of Conformity	DE PI830000 160627 001
Engineering Data	CAD data – STEP CAD data – DWG CAD data – DXF
Catalogues	Catalogues in PDF-format

CB 365/7,5 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

