

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD	
	A	RELEASED	RSA-10-091-01	10SEP2010	NCL	DAO
	AI	REVISED BY	ECO-10-023502	17NOV2010	NCL	ASV

29,5

28,85

3,1

4,8

11,8

11,8

4,1

1,2

8,6

LOGOTIPO TE

TE LOGO

1- TERMINAL APLICÁVEL NÚMERO: 353376
(BITOLA DO CABO: AVSS,CAVS 0,3~0,5mm²)
FERRITE APLICÁVEL NÚMERO: 353379.

2- ESTE PRODUTO DEVE SER UTILIZADO COM O
11 DIA SQUIB MK-2 SLIM PLUG HSG
TRAVAMENTO INFERIOR (NÚMERO 1612119).

3- MONTAR ANEL CURTO-CIRCUITO
NÚMERO DA PEÇA: 699638,1376766,1473369.

4- FORMA DE INTERFACE VER O
DESENHO DO ANEL DE CURTO-CIRCUITO.

5- FOLHA DE INSTRUÇÃO: 411-78040.

1- APPLICABLE TERMINAL P/N: 353376
(WIRE RANGE: AVSS,CAVS 0,3~0,5mm²)
APPLICABLE FERRITE P/N: 353379.

2- THIS PRODUCT SHOULD BE USED WITH
THE 11 DIA SQUIB SLIM MK-2 PLUG HSG
LOCKING BUTTON (P/N: 1612119).

3- MATING SHORT-CIRCUIT RING
PART NUMBER: 699638, 1376766, 1473369.

4- ABOUT THE FORM OF INTERFACE, SEE THE
DRAWING OF SHORT-CIRCUIT RING.

5- INSTRUCTION SHEET: 411-78040.

AMARELO/YELLOW

C

TRIBIT 1503(K)

1612120 -4

FINISH

RIB POS

MATERIAL

PART NUMBER

DWN
NCLAPRESA
CHK
JRGOLDSCHMIDT
APVD
DAO LVEIRA

10SEP2010
10SEP2010
10SEP2010

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

Tyco Electronics

TYCO ELECTRONICS Brasil LTDA.

Sao Paulo, Brasil

NAME
11 DIA SQUIB SLIM
MK-2 PLUG HSG
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1612120-4

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
3:1

SHEET
1

OF
1

REV
AI

0 PLC ±-
1 PLC ±0,2
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±1°

FINISH
SEE TABLE

DIMENSIONS:
mm

PERSPECTIVE VIEW

SCALE 1:1

"A"

"B"

"C"

POSIÇÃO RIB
RIB POSITION

1470-19 (2/09)