


SPECIFICATION CONTROL DRAWING		4126C1332
CHEMINAX	41 OHM, AWG 26, 19 STRANDS OF AWG 38, COAXIAL CABLE	Date: 8-4-15 Revision: C
THIS SPECIFICATION SHEET FORMS A PART OF THE LATEST ISSUE OF RAYCHEM SPECIFICATION 1200.		
CONSTRUCTION DETAILS		ELECTRICAL CHARACTERISTICS
DIMENSIONS ARE NOMINAL VALUES IN INCHES, UNLESS OTHERWISE DESIGNATED. 		CHARACTERISTIC IMPEDANCE 41 ± 2 ohms, Method A CAPACITANCE 35.3 pF/ft. (minimum), 42.0 pF/ft. (maximum) VELOCITY OF PROPAGATION 64% (nominal)
		ADDITIONAL REQUIREMENTS
		ELECTRICAL CONDUCTOR RESISTANCE 36.4 ohms/1000 ft. (nominal) INSULATION RESISTANCE 10,000 megohms (minimum) for 1000 ft. JACKET FLAWS SPARK TEST 1.0 kV (rms) IMPULSE TEST 6.0 kV (peak) VOLTAGE WITHSTAND (DIELECTRIC) 1500 volts (rms)
		ENVIRONMENTAL FLAMMABILITY Method C HEAT SHOCK 225°C LOW TEMPERATURE-COLD BEND -55°C/2.50 inch mandrel VOLTAGE WITHSTAND (Post Environmental) 1000 volts (rms), 1 minute
		PHYSICAL INSULATION (DIELECTRIC) ELONGATION 200% (minimum) TENSILE STRENGTH 1800 lbf/in ² (minimum) JACKET ELONGATION 200% (minimum) TENSILE STRENGTH 2000 lbf/in ² (minimum) JACKET THICKNESS .010 inch (nominal) SHIELD COVERAGE 90% (minimum)
Designate outer jacket color with a dash number in accordance with MIL-STD-681. Unless otherwise specified, outer jacket color will be black designated by a "-0" appended to the part number, (e.g. 4126C1332-0). Other codes and suffixes may be added to the part number, as necessary, to capture any additional requirements imposed by the purchase order.		WEIGHT 7.3 lbs/1000 ft. (nominal)
		ENGINEERING REFERENCE TEMPERATURE RATING 110°C (maximum)
Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.		
Page 1 of 1	Rayolin, Thermorad, Cheminax, Raychem, TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks.	



Raychem Wire & Cable
 501 Oakside Avenue
 Redwood City, California 94063-3800
 Phone: 1-800-227-8816 Fax: 1-650-361-6297

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.
 REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

© 2007-2015 Tyco Electronics Corporation. All rights reserved.