

**CD-HF 50X75 5/7.5 DKG Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Orders on request only

**Similar to illustration**

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

**General ordering data**

|                 |                                                                    |
|-----------------|--------------------------------------------------------------------|
| Version         | Halogen-free cable duct, 50 mm x 75 mm, 5.00 mm x 7.50 mm, 2000 mm |
| Order No.       | <a href="#">2589360000</a>                                         |
| Type            | CD-HF 50X75 5/7.5 DKG Y                                            |
| GTIN (EAN)      | 4050118603453                                                      |
| Qty.            | 24 m                                                               |
| Delivery status | Discontinued                                                       |

**CD-HF 50X75 5/7.5 DKG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Height     | 50 mm    | Height (inches) | 1.969 inch |
| Width      | 75 mm    | Width (inches)  | 2.953 inch |
| Length     | 2,000 mm | Length (inches) | 78.74 inch |
| Net weight | 529 g    |                 |            |

**Temperatures**

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -25...120 °C |
|-----------------------------|--------------|

**General information**

|                           |                                 |                             |                                         |
|---------------------------|---------------------------------|-----------------------------|-----------------------------------------|
| Colour                    | dark grey                       | Flexible wiring duct        | No                                      |
| Halogen                   | No                              | Included in delivery        | Cable duct, Lid                         |
| Lid                       | Yes                             | Material                    | PPE                                     |
| Non-tracking              | Yes                             | Operating temperature range | -25...120 °C                            |
| Slit gap                  | 7.5 mm                          | Slit width                  | 5 mm                                    |
| Standards                 | In accordance with DIN EN 50085 | Type of mounting            | when screwed in, With adhesive, Riveted |
| UL 94 flammability rating | V-0                             | Usable cross-section        | 3,220 mm <sup>2</sup>                   |
| Version of side panel     | slotted                         |                             |                                         |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000012    | ETIM 7.0    | EC000012    |
| ETIM 8.0    | EC000012    | ETIM 9.0    | EC000012    |
| ETIM 10.0   | EC000012    | ECLASS 9.1  | 27-40-07-03 |
| ECLASS 10.0 | 27-40-07-03 | ECLASS 11.0 | 27-40-07-03 |
| ECLASS 12.0 | 27-40-07-03 | ECLASS 13.0 | 27-40-07-03 |
| ECLASS 14.0 | 27-40-07-03 | ECLASS 15.0 | 27-40-07-03 |

**Approvals**

Approvals



|                       |                                                                                                                                                                             |
|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approvals MAMID       | <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319262/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319262/-T1z1mm-S800/</a> |
| ROHS                  | Conform                                                                                                                                                                     |
| UL File Number Search | UL Website                                                                                                                                                                  |
| Certificate No. (UR)  | E500004                                                                                                                                                                     |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Downloads**



|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|

## CD-HF 50X75 5/7.5 DKG

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



**CD-HF 50X75 5/7.5 DKG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Flat**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

|            |                            |                                    |
|------------|----------------------------|------------------------------------|
| Type       | CD-RET 100/120             | Version                            |
| Order No.  | <a href="#">2554060000</a> | Cable duct binder, 2.8 mm x 126 mm |
| GTIN (EAN) | 4050118564181              |                                    |
| Qty.       | 250 pc(s).                 |                                    |

**Dark grey**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

|            |                            |                         |
|------------|----------------------------|-------------------------|
| Type       | CD-LID 75 DKG              | Version                 |
| Order No.  | <a href="#">2589020000</a> | Cable duct cover, 75 mm |
| GTIN (EAN) | 4050118602418              |                         |
| Qty.       | 2 m                        |                         |

## CD-HF 50X75 5/7.5 DKG

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Rivet and cover

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



#### General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | EXRV 6.5                   | Version                    |
| Order No.  | <a href="#">2562690000</a> | Expanding rivet, 32 mm x   |
| GTIN (EAN) | 4050118571639              |                            |
| Qty.       | 1,000 pc(s).               |                            |
| Type       | EXRV-T 4.5                 | Version                    |
| Order No.  | <a href="#">2562720000</a> | Expanding-rivet tool       |
| GTIN (EAN) | 4050118571578              |                            |
| Qty.       | 4 pc(s).                   |                            |
| Type       | EXRV 4.5                   | Version                    |
| Order No.  | <a href="#">2562700000</a> | Expanding rivet, 27.5 mm x |
| GTIN (EAN) | 4050118571622              |                            |
| Qty.       | 1,000 pc(s).               |                            |
| Type       | EXRV-T 6.5                 | Version                    |
| Order No.  | <a href="#">2562710000</a> | Expanding-rivet tool       |
| GTIN (EAN) | 4050118571615              |                            |
| Qty.       | 4 pc(s).                   |                            |

### Side arm

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



#### General ordering data

|            |                            |                                        |
|------------|----------------------------|----------------------------------------|
| Type       | CD-RETA                    | Version                                |
| Order No.  | <a href="#">2554080000</a> | Cable duct binder arm, 8 mm x 115.3 mm |
| GTIN (EAN) | 4050118564204              |                                        |
| Qty.       | 100 pc(s).                 |                                        |

**CD-HF 50X75 5/7.5 DKG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Marking**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

|            |                            |                                     |
|------------|----------------------------|-------------------------------------|
| Type       | CD-LB                      | Version                             |
| Order No.  | <a href="#">2562680000</a> | Cable duct tag rail, 15 mm x        |
| GTIN (EAN) | 4050118571646              |                                     |
| Qty.       | 150 pc(s).                 |                                     |
| Type       | CD-LBK                     | Version                             |
| Order No.  | <a href="#">2554120000</a> | Cable duct tag rail kit, 30 mm x    |
| GTIN (EAN) | 4050118564242              |                                     |
| Qty.       | 20 pc(s).                  |                                     |
| Type       | CD-LBH                     | Version                             |
| Order No.  | <a href="#">2562850000</a> | Cable duct tag rail holder, 30 mm x |
| GTIN (EAN) | 4050118571691              |                                     |
| Qty.       | 150 pc(s).                 |                                     |