

**P BAG XL SET 13****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

**General ordering data**

|                 |                                                                |
|-----------------|----------------------------------------------------------------|
| Version         | Tools, Accessories                                             |
| Order No.       | <a href="#">2602230000</a>                                     |
| Type            | P BAG XL SET 13                                                |
| GTIN (EAN)      | 4050118657814                                                  |
| Qty.            | 1 pc(s).                                                       |
| Delivery status | <b>This article will no longer be available in the future.</b> |
| Available until | 2026-02-28                                                     |

**P BAG XL SET 13****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 220 mm  | Depth (inches)  | 8.661 inch  |
| Height     | 60 mm   | Height (inches) | 2.362 inch  |
| Width      | 320 mm  | Width (inches)  | 12.598 inch |
| Net weight | 1,809 g |                 |             |

**Technical data**

|                        |                 |
|------------------------|-----------------|
| Description of article | Toolbag, fitted |
|------------------------|-----------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000181    | ETIM 7.0    | EC000181    |
| ETIM 8.0    | EC000181    | ETIM 9.0    | EC000181    |
| ETIM 10.0   | EC000181    | ECLASS 9.0  | 21-10-01-90 |
| ECLASS 9.1  | 21-10-01-90 | ECLASS 10.0 | 21-10-01-90 |
| ECLASS 11.0 | 21-10-01-90 | ECLASS 12.0 | 21-10-01-90 |
| ECLASS 13.0 | 21-10-01-90 | ECLASS 14.0 | 21-10-01-90 |
| ECLASS 15.0 | 21-10-01-90 |             |             |

**Environmental Product Compliance**

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 7a, 7cl                              |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 1eacbb3e-7931-4ebb-9179-f29fd9b50028 |

**Downloads**

|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|

**P BAG XL SET 13****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****VDE-insulated combination pliers**

When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

**General ordering data**

|            |                            |         |
|------------|----------------------------|---------|
| Type       | KBZ 180                    | Version |
| Order No.  | <a href="#">9046290000</a> | Pliers  |
| GTIN (EAN) | 4032248356485              |         |
| Qty.       | 1 pc(s).                   |         |

**with LED Display**

The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE standard
- high peak voltage strength
- the right tester for every application

**General ordering data**

|            |                            |                                      |
|------------|----------------------------|--------------------------------------|
| Type       | VT COMBI PRO               | Version                              |
| Order No.  | <a href="#">9918860000</a> | Testing tools, 2-pole voltage tester |
| GTIN (EAN) | 4032248405749              |                                      |
| Qty.       | 1 pc(s).                   |                                      |

## P BAG XL SET 13

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## unfitted




Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

## General ordering data

|            |                            |                    |
|------------|----------------------------|--------------------|
| Type       | P BAG BIG                  | Version            |
| Order No.  | <a href="#">2576620000</a> | Tools, Accessories |
| GTIN (EAN) | 4050118650594              |                    |
| Qty.       | 1 pc(s).                   |                    |

## Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

## General ordering data

|            |                            |                                                                                           |
|------------|----------------------------|-------------------------------------------------------------------------------------------|
| Type       | SDIS SLIM 0.8X4.0X100      | Version                                                                                   |
| Order No.  | <a href="#">2749620000</a> | Mounting tool, Blade width (B): 4 mm, Blade length: 100 mm, Blade thickness (A): 0.8 mm   |
| GTIN (EAN) | 4050118896367              |                                                                                           |
| Qty.       | 1 pc(s).                   |                                                                                           |
| Type       | SDIS SLIM 0.6X3.5X100      | Version                                                                                   |
| Order No.  | <a href="#">2749610000</a> | Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade thickness (A): 0.6 mm |
| GTIN (EAN) | 4050118896350              |                                                                                           |
| Qty.       | 1 pc(s).                   |                                                                                           |

## P BAG XL SET 13

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Crosshead screwdriver, Phillips



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | SDIK SLIM PH2 X 100        | Version                                                            |
| Order No.  | <a href="#">2749660000</a> | Screwdriver, Blade width (B): 2 mm, 100 mm, Blade thickness (A): 2 |
| GTIN (EAN) | 4050118896404              |                                                                    |
| Qty.       | 1 pc(s).                   |                                                                    |
| Type       | SDIK SLIM PH1 X 80         | Version                                                            |
| Order No.  | <a href="#">2749650000</a> | Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1  |
| GTIN (EAN) | 4050118896398              |                                                                    |
| Qty.       | 1 pc(s).                   |                                                                    |

## Tools



- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm<sup>2</sup> to 5 x 2.5 mm<sup>2</sup>
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

## General ordering data

|            |                            |                     |
|------------|----------------------------|---------------------|
| Type       | STRIPPER ROUND TOP         | Version             |
| Order No.  | <a href="#">9918050000</a> | Sheathing strippers |
| GTIN (EAN) | 4032248359165              |                     |
| Qty.       | 1 pc(s).                   |                     |

**P BAG XL SET 13****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Tools**

- Simple, fast and accurate stripping of insulation of all conventional round cables from 4 to 37 mm<sup>2</sup>
- Knurled screw at end of handle for setting the cutting depth (setting the cutting depth prevents damage to inner conductor)

**General ordering data**

|            |                            |                     |
|------------|----------------------------|---------------------|
| Type       | SLICER NO 16               | Version             |
| Order No.  | <a href="#">9918070000</a> | Sheathing strippers |
| GTIN (EAN) | 4032248359189              |                     |
| Qty.       | 1 pc(s).                   |                     |

**Cutting tools**

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

**General ordering data**

|            |                            |                                                    |
|------------|----------------------------|----------------------------------------------------|
| Type       | KT 8                       | Version                                            |
| Order No.  | <a href="#">9002650000</a> | Cutting tools, Cutting tool for one-hand operation |
| GTIN (EAN) | 4008190020163              |                                                    |
| Qty.       | 1 pc(s).                   |                                                    |

**P BAG XL SET 13****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Tools**

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

**General ordering data**

|            |                            |                                   |
|------------|----------------------------|-----------------------------------|
| Type       | STRIPAX                    | Version                           |
| Order No.  | <a href="#">9005000000</a> | Tools, Stripping and cutting tool |
| GTIN (EAN) | 4008190072506              |                                   |
| Qty.       | 1 pc(s).                   |                                   |