



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
J			B	REVISED PER ECR-10-010439	04JUN2010	HMR

1. MATERIAL: CASE: ZINC
RUBBER: NITRILE-BUTADIENE RUBBER
COLOR: BLACK
SPRING: STAINLESS STEEL
HOUSING: POLYBUTYLEN TEREPHTHALATE (94V-0)
COLOR: BLACK

2. FINISH(CASE): NICKEL OVER COPPER PLATING
3. THE SHAPE, SIZE AND POSITION OF THE CHARACTER
SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

4. APPLY TO COMMERCIAL-RELEASE CABLE GLAND (M20)
FOR WATERPROOFING AND HOLDING OF CAPTYRE CABLE.

- I : AS SHOWN






LOGO MARK

1. 材料: ケース: 亜鉛
ゴム: ニトリルブタジエンゴム
色: 黒
スプリング: ステンレス
ハウジング: ポリアチレンテレフタレート(94V-0)
色: 黒

2. 仕上げ: 銅下地めっきの上に、ニッケルめっき仕上げ
3. 文字の形状、大きさ、および位置については、大略を示すものであり、
詳細を示すものではありません。

4. キャプタイヤケーブルの防水と保持には、市販のケーブルグランド(M20)を使用ください。



4 有効ネジ長10mm
SCREW LENGTH
VALID FOR 10mm

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN T. SAMI	15MAR2007	 Tyco Electronics Corporation Kawasaki, Japan	
		CHK D. MITSUGI	15MAR2007		
		APVD D. MITSUGI	15MAR2007		
		PRODUCT SPEC 製品規格	108-78417		
		APPLICATION SPEC 取付適用規格	411-78262, 78287	NAME 名称 MULTIPLE ENCLOSURE CONN, M PLUG CASE ASSY	
		WEIGHT	143.37 g		
DIMENSIONS: 単位: 概 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±3°		SIZE	RESTRICTED TO
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		CAGE CODE	REV
MATERIAL 材料		FINISH 仕上		DRAWING NO 番号	
1		2		A300779	
		CUSTOMER DRAWING		SCALE 尺度	
				SHEET	
				OF	
				REV	B