

IE-PH-V01P-BP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Bayonet plug-in connectors according to IEC
61076-3-106 ver.1 (Ethernet/IP), plastic, empty housing

General ordering data

Version	Empty enclosure, Plug housing, bending protection, IP67
Order No.	1012460000
Type	IE-PH-V01P-BP
GTIN (EAN)	4032248720118
Qty.	10 pc(s).

IE-PH-V01P-BP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	126 mm	Depth (inches)	4.961 inch
Height	30 mm	Height (inches)	1.181 inch
Width	30 mm	Width (inches)	1.181 inch
Net weight	32 g		

Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

General data

Colour		Configuration	Plug housing with labelling/marketing holder: 9*11 mm; suitable for holding RJ45 and fibre-optic inserts
	Miscellaneous		
Housing main material	PA UL 94 V0	Plugging cycles	750
Protection degree	IP67		

General standards

Connector standard	IEC 61076-3-106 Var. 1
--------------------	------------------------

Classifications

ETIM 6.0	EC001031	ETIM 7.0	EC001031
ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 9.0	27-18-27-02
ECLASS 9.1	27-18-27-02	ECLASS 10.0	27-18-27-02
ECLASS 11.0	27-18-27-02	ECLASS 12.0	27-18-27-02
ECLASS 13.0	27-19-01-04	ECLASS 14.0	27-19-01-04
ECLASS 15.0	27-19-01-04		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	11b17e97-f803-4c09-9278-b20f22f15f81

Approvals

ROHS	Conform
------	---------

IE-PH-V01P-BP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Con-
formity

[DUXR.E316369](#)

Engineering Data

[CAD data – STEP](#)

Product Change Notification

[20210412 Technical change for cap nut V1 and V4](#)

[20210412 Technische Änderung zu Hutmutter V1 und V4](#)

User Documentation

[MAN IE GUIDE DE](#)

[MAN IE GUIDE EN](#)

[Designation key / Type key](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[MB FREECONTACT EN](#)

[FL FIELDWIRING EN](#)

[PI PROFINET CABLING EN](#)

[PI PROFINET CABLING EN](#)

IE-PH-V01P-BP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing

