

## SLEP 2C 6

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

|            |                                                                                               |
|------------|-----------------------------------------------------------------------------------------------|
| Version    | End plate for terminals, dark beige, Height: 62.8 mm, Width: 2.2 mm, V-0, Wemid, Snap-on: Yes |
| Order No.  | <a href="#">3037590000</a>                                                                    |
| Type       | SLEP 2C 6                                                                                     |
| GTIN (EAN) | 4099987000406                                                                                 |
| Qty.       | 50 pc(s).                                                                                     |

**SLEP 2C 6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 36 mm   | Depth (inches)  | 1.417 inch |
| Height     | 62.8 mm | Height (inches) | 2.472 inch |
| Width      | 2.2 mm  | Width (inches)  | 0.087 inch |
| Net weight | 3.8 g   |                 |            |

**Temperatures**

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 130 °C        |

**Material data**

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Material                  | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0   |        |            |

**System specifications**

|         |           |
|---------|-----------|
| Version | End plate |
|---------|-----------|

**Additional technical data**

|         |     |                   |     |
|---------|-----|-------------------|-----|
| Snap-on | Yes | With snap-in pegs | Yes |
|---------|-----|-------------------|-----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000886    | ETIM 7.0    | EC000886    |
| ETIM 8.0    | EC000886    | ETIM 9.0    | EC000886    |
| ETIM 10.0   | EC000886    | ECLASS 9.1  | 27-14-11-33 |
| ECLASS 10.0 | 27-14-11-33 | ECLASS 11.0 | 27-14-11-33 |
| ECLASS 12.0 | 27-14-11-33 | ECLASS 13.0 | 27-25-03-01 |
| ECLASS 14.0 | 27-25-03-01 | ECLASS 15.0 | 27-25-03-01 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Downloads**

|                  |                                 |
|------------------|---------------------------------|
| Engineering Data | <a href="#">CAD data – STEP</a> |
|------------------|---------------------------------|