

IE-PI-SCRJ-SM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

FO SC inserts for plug-in connectors ver.1 / 4 / 14

General ordering data

Version	SC insert, Plug SCRJ, singlemode
Order No.	1067390000
Type	IE-PI-SCRJ-SM
GTIN (EAN)	4032248820863
Qty.	10 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2025-04-08

IE-PI-SCRJ-SM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	56 mm	Depth (inches)	2.205 inch
Height	10.5 mm	Height (inches)	0.413 inch
Width	13.2 mm	Width (inches)	0.52 inch
Net weight	19.4 g		

Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

General data

Colour		Configuration	Connector and flange insert for variant 1, 4 and 14 housings
	Miscellaneous		
Connection 1	SCRJ	Connection 2	Crimp
Description of article	Plug SCRJ, singlemode	Ferrule material	Zirconia
Fibre type	Singlemode	Housing main material	Zinc diecast, PA
Insertion loss	≤ 0.5 dB	Plugging cycles	1000
Protection degree	IP67 with housing	Return loss (attenuation)	≥ 40 dB

General standards

Certificate No. (UL)	E477798	Connector standard	IEC 61754-24
----------------------	---------	--------------------	--------------

Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ETIM 9.0	EC001122
ETIM 10.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22
ECLASS 13.0	19-17-01-22	ECLASS 14.0	19-17-01-22
ECLASS 15.0	19-17-01-22		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319261/-T1z1mm-S800/
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UL)	E477798

IE-PI-SCRJ-SM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN Designation key / Type key
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-PI-SCRJ-SM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing

