

IE-FM5D2UE0350MSD0SD0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Industrial Ethernet connection technology by Weidmüller offers the optimal solution for the infrastructure of your machine, system or factory. All connection technology is available from one source.

The benefits for you:

- IEC-standardised connectors, in the variants 1, 4, 5 , 6 and 14
- consistently Cat. 6_A with **STEADYTEC®** technology
- in IP20 and IP67
- all relevant industrial connections: RJ45, SC, ...
- comprehensive range of accessories

General ordering data

Version	Dragline cable, SC duplex IP 20, SC duplex IP 20, 50 µm, PUR, 350 m
Order No.	8876433500
Type	IE-FM5D2UE0350MSD0SD0X
GTIN (EAN)	4032248744596
Qty.	1 pc(s).

IE-FM5D2UE0350MSD0SD0X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	350 m	Length (inches)	13,779.527 inch
Net weight	5,000 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-20 °C...60 °C		

General standards

Connector standard	IEC 61754-4
--------------------	-------------

Fibre-optic

Attenuation	2.3 dB/km at 850 nm, ≤ 0.5 dB/km at 1300 nm	Bandwidth	500 MHz*km at 850 nm, 500 MHz*km at 1300 nm
Fibre type	GOF, Multimode, OM2	Insertion loss	≤ 0.4 dB
Return loss (attenuation)	≥ 30 dB		

Cable structure

Cable layout	Break-out dragline	Core diameter	50 µm
Material sheath	PUR	Primary coating	245 µm
Sheath diameter	6 mm	Sheathing colour	black

Mechanical and material properties of cable

Bending cycles	100,000	Halogen	No
Min. bending radius, once only	25 mm	Min. bending radius, repetitive	77 mm

Classifications

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 9.0	27-06-10-03
ECLASS 9.1	27-06-10-03	ECLASS 10.0	27-06-10-03
ECLASS 11.0	27-06-10-03	ECLASS 12.0	27-06-10-03
ECLASS 13.0	27-06-10-03	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

IE-FM5D2UE0350MSD0SD0X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN