

BG ARGH HQP ALU PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**HQ adapter for FieldPower®**

Tool-free installation like a FieldPower cable seal

Suitable for the HQ 4/2, HQ 8 and HQ 17 plug-in connector inserts

Optionally with lockable protective cover (protection against being switched on again, in accordance with EN 60204-1)

General ordering data

Version	Adapter, Field Power® sealing insert, HQ adapter, IP65, with corresponding enclosure, Polycarbonate, glass fibre reinforced, lockable: No
Order No.	1532200000
Type	BG ARGH HQP ALU PT6
GTIN (EAN)	4050118337433
Qty.	1 pc(s).

Creation date June 13, 2025 8:07:15 AM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.

BG ARGH HQP ALU PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	60.11 mm	Depth (inches)	2.367 inch
Height	39 mm	Height (inches)	1.535 inch
Width	58 mm	Width (inches)	2.283 inch
Net weight	34.99 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...70 °C
---------------------	----------------	-----------------------	----------------

General data

Mounting position, installation notice	in FieldPower® sealing slot	Protection degree	IP65, with corresponding enclosure
Silicone	No	UL 94 flammability rating	HB

Version

Design	HQ adapter
--------	------------

Classifications

ETIM 6.0	EC002624	ETIM 7.0	EC002624
ETIM 8.0	EC002624	ETIM 9.0	EC002624
ETIM 10.0	EC002624	ECLASS 9.1	27-18-27-90
ECLASS 10.0	27-18-28-15	ECLASS 11.0	27-18-28-15
ECLASS 12.0	27-18-28-15	ECLASS 13.0	27-18-28-15
ECLASS 14.0	27-18-28-15	ECLASS 15.0	27-18-28-15

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	210f646e-64fd-46de-9a7c-8dff222ea2cb

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

Downloads

Approval/Certificate/Document of Conformity	UL Certificate FieldPower® HQ adapter Manufacturer's Declaration FieldPower® plug-in connectors and HQ adapters
Engineering Data	CAD data – STEP Success story – FieldPower® customer reference PRO-EL Success story – FieldPower® Kundenreferenz PRO-EL
Product Change Notification	Product Change Notification FieldPower® HQ Adapter Produktänderungsmitteilung FieldPower® HQ Adapter
Catalogues	Catalogues in PDF-format

Creation date June 13, 2025 8:07:15 AM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.

2