



Industry Applications.



Bulgin is widely recognised as a leading manufacturer of environmentally sealed connectors & components.

With over 95 years of experience in the industry, Bulgin continues to innovate & develop products and services to cater for its global customer base across a variety of markets.

Marine.

A large white yacht with a dark blue stripe along the waterline is sailing on dark blue water. The boat is angled towards the right, with its bow cutting through the water. The background is a dark, hazy sky.

Marine applications such as ship deck systems, marina facilities and boating equipment are constantly exposed to the harshest of conditions. With high corrosion and water ingress posing a constant threat to connectivity solutions, sealed and robust components are a must for applications in this market.

Originally designed for leisure yachts, our Buccaneer connector range is perfectly suited to meet the challenging requirements of marine applications both above and below water level.



Above Water.

Surface marine applications such as ship deck systems, marina facilities and boating equipment are constantly exposed to the harshest of conditions. With high corrosion and water ingress posing a constant threat to connectivity solutions, sealed and robust components are a must for applications in this market. Originally designed for leisure yachts, our Buccaneer connector range is perfectly suited to meet the challenging requirements of marine applications both above and below water level.

With a wide portfolio of IP rated power, signal and data connectors, along with years of experience in designing and manufacturing sealed interconnect solutions, we are sure to have the right solution for your marine connectivity needs. If our existing product range doesn't meet your specifications then our experienced engineering teams have the knowledge and expertise needed to create a custom solution specific to your unique requirements.

- Boat & Yacht Lighting
- Water Quality Systems
- GPS Marine Equipment
- Container Ship Communication
- LED Marine Lanterns
- Unmanned Surface Vehicles (USV)
- Water Flow Data Loggers
- Marina Energy Distribution Units
- Sailboats



Products Related To This Industry:

6000 Series

Circular Power Connectors



- 2 - 22 Contacts
- Plastic or Metal Housing
- IP66, IP67, IP68 & IP69K protection
- Secure, quick mating / release
- cULus, UL, VDE Approvals

400 Series

Circular Power Connectors



- Ratings up to 8A, 250V ac/dc
- 2, 3, 4, 6, 8, 10 & 12 contacts
- IP66, IP67, IP68 & IP69K protection
- Pin or socket, screw thread locking
- CE, UL, CSA & VDE approvals

Standard Series USB

Circular Data Connectors



- USB V2.0 performance
- IP66, IP67, IP68 & IP69K protection
- USB type 'A' or 'B' configurations
- Single & double ended cable / panel mount options

400 Series Mini USB

Circular Data Connectors



- Sealed Mini-USB cable connectors
- Data rates up to 480Mbps
- IP66, IP67, IP68 & IP69K protection
- USB V2.0 performance
- Front + rear & PCB panel mount options

Standard Ethernet

Circular Data Connectors



- Cat5e RJ45 Ethernet Connectors
- Data rates up to 100MHz
- IP66, IP67, IP68 & IP69K protection
- Shielded system
- Noise immunity & EMI protection

Vandal Resistant

Switches



- High corrosion resistance
- Domed, low & prominent profiles
- IP66 & IP68 sealing versions
- Illuminated & non-illuminated
- Front & rear panel mount versions

Standard Series

Circular Power Connectors



- Rating up to 12A, 277V ac/dc
- 2, 3, 4, 6, 7, 9, 12 & 25 contacts
- IP66, IP67, IP68 & IP69K protection
- Plug & receptacle connectors
- CCC, UL, CSA & VDE approvals

400 Series SMB

Circular Data Connectors



- 50Ω impedance SMB antenna
- Frequency range 0 - 4GHz
- IP66, IP67, IP68 & IP69K protection
- Rewireable & pre-wired options
- RG-174 cables

Underwater.

Operating underwater requires the most rugged and reliable of connectivity components. Pressure, extreme temperatures and salt water all pose complex challenges for underwater marine applications. With more companies seeking to go deeper for longer in such hostile conditions due to production and exploratory reasons, increasing the life cycles of submersible connectors and simplifying product maintenance processes is more important than ever before.

With a high risk of corrosion affecting the integrity of power, signal and data connections, sealed connector solutions are a must for high performance underwater marine equipment. Bulgin's expertise in producing environmentally sealed connectors makes us one of the world's interconnect leaders for marine application solutions where immersion is required in low and high pressure underwater environments.

- Sealed Diving Cameras
- Diver Communications

- Depth Loggers
- Subsea ROV



Products Related To This Industry:

4000 Micro USB

Circular Data Connectors



- Data rates up to 480Mbs
- USB V2.0 performance
- IP66, IP67, IP68 & IP69K protection
- EN60068-2-52 Test Kb Salt Mist (Cyclic) Marine Severity Level 1

6000 Series

Circular Power Connectors



- 2 - 22 Contacts
- Plastic or Metal Housing
- IP66, IP67, IP68 & IP69K protection
- Secure, quick mating / release
- cULus, UL, VDE Approvals

400 Series

Circular Power Connectors



- Ratings up to 8A, 250V ac/dc
- 2, 3, 4, 6, 8, 10 & 12 contacts
- IP66, IP67, IP68 & IP69K protection
- Pin or socket, screw thread locking
- CE, UL, CSA & VDE approvals

400 Series Mini USB

Circular Data Connectors



- Sealed Mini-USB cable connectors
- Data rates up to 480Mbs
- IP66, IP67, IP68 & IP69K protection
- USB V2.0 performance
- Front + rear & PCB panel mount options

400 Series SMB

Circular Data Connectors



- 50Ω impedance SMB antenna
- Frequency range 0 - 4GHz
- IP66, IP67, IP68 & IP69K protection
- Rewireable & pre-wired options
- RG-174 cables

7000 Series

Circular Power Connectors



- Ratings up to 25A, 600V
- 2, 3, 6, 10 & 32 contacts
- IP66, IP67, IP68 and IP69K rated
- Plastic Shells
- cULus, UL & VDE approvals

Standard Ethernet

Circular Data Connectors



- Cat5e RJ45 Ethernet Connectors
- Data rates up to 100MHz
- IP66, IP67, IP68 & IP69K protection
- Shielded system
- Noise immunity & EMI protection

ROV Tether Connector

Circular Power / Data Connectors



- 316 Stainless Steel Construction
- Pressure Balanced Oil Filled (PBOF)
- Data, Power & Fibre Optics
- Ratings up to 5KV, 32A
- Capable of up to 7000m subsea depths

Bulgin has you covered.

**Our components are available through a
large network of National and International
Distributors Worldwide.**

Search for stock at:

www.bulgin.com/products/stock



www.bulgin.com

Europe

Bulgin
200 Cambridge Science Park
Milton Road
Cambridge, CB4 0GZ, UK
tel: +44 (0) 1803 407757
e: info@bulgin.com

Americas

Bulgin
11849 Telegraph Road
Santa Fe Springs
CA 90670, USA
tel: +1 760-343-3650
e: info@bulgin.com

Asia Pacific

Bulgin
11849 Telegraph Road
Santa Fe Springs
CA 90670, USA
tel: +1 760-343-3650
e: info@bulgin.com