

**WORKPLACE
SOLUTIONS**

Weidmüller 



Workplace Solutions

Cut it. Strip it. Crimp it.

The new Stripax[®] Plus – now even easier

We have completely transformed our flagship multifunctional tool. The new Stripax[®] Plus can cut, strip, and crimp single wires in the cross-section range from AWG 20 to 14 (0.5 to 2.5 mm²).

The wire-end ferrules are stored in a magazine in the handle and are automatically transported to the crimping die. Adjustments to different cross-sections are made automatically so that no manual adjustment is required.



Cutting



Stripping



Crimping



For more information, visit our website:
www.weidmuller.com/crimping

The New Stripax® Plus – Increase Efficiency and Productivity

Time-saving. Space-saving. All-in-one solution.

In field operations, there is often little space in the toolbox.
That's why multifunctional tools like our Stripax® Plus are useful.
With this tool, cutting, stripping, and crimping are quick and easy.

Universal crimping die
AWG 20 to 14 (0.5 to 2.5 mm²)

Automatic ferrule
transportation

Ferrules stored inside
the handle

Self adjusting
stripping unit

Stripping length
adjustable via end stop

Cutting cables up to
AWG 14 (2.5 mm²)

Special designed wire-end
ferrules with 50 pcs in a line



Type	Order No.
STRIPAX PLUS 2.5	9020000000
STRIPAX PLUS 2.5 ZERT	9011980000

Wire-end ferrules

Weidmuller color code

Type	Ø mm²	Sleeve length	Color	Qty.	Order No.
H0,5/14 OR BD	0.5	8 mm	orange	500	9004270000
H0,75/14 W BD	0.75	8 mm	white	500	9004290000
H1,0/14 GE BD	1	8 mm	yellow	500	9004320000
H1,5/14 R BD	1.5	8 mm	red	500	9004340000
H2,5/14D BL BD	2.5	8 mm	blue	500	9004360000

DIN color code

Type	Ø mm²	Sleeve length	Color	Qty.	Order No.
H0,5/14D W BD	0.5	8 mm	white	500	9004280000
H0,75/14D GR BD	0.75	8 mm	gray	500	9004300000
H1,0/14D R BD	1	8 mm	red	500	9004330000
H1,5/14D SW BD	1.5	8 mm	black	500	9004350000
H2,5/14D BL BD	2.5	8 mm	blue	500	9004360000

Telemecanique color code

Type	Ø mm²	Sleeve length	Color	Qty.	Order No.
H0,5/14T W BD	0.5	8 mm	white	500	9021930000
H0,75/14T HBL BD	0.75	8 mm	light blue	500	9004310000
H1,0/14T R BD	1	8 mm	red	500	9021950000
H1,5/14T SW BD	1.5	8 mm	black	500	9021960000
H2,5/14T GR BD	2.5	8 mm	gray	500	9004370000

Weidmuller, Inc
821 Southlake Blvd.
Richmond, Virginia 23236
Telephone: (800) 849-9343
Email: customerservice@weidmuller.com
Website: www.weidmuller.com