

ATC, ATM and ATR fuse blocks



Additional power for your fused accessories



Bussmann series splash proof fuse blocks for ATC, ATM and ATR fuses are versatile, durable and easy to install.

Product description:

Bussmann® series fuse blocks offer customers a cost-effective solution for adding multiple fused circuits in one compact package.

These fuse blocks are available in 4-, 6-, 8- and 10-pole versions for ATC, ATM and the new micro ATR fuses. They provide an inexpensive alternative for smaller installations and replace traditional glass tube fuse blocks.

Designed for versatility and durability, Bussmann series fuse blocks are an easy-to-install solution. What's more, with multiple pole configurations, customers have the flexibility to choose the right fuse block to meet their needs.

Features and benefits:

- Clear, plastic cover for fast visual confirmation of fuse amp rating, and easy identification of blown fuses when Bussmann series *easyID™* ATC and ATM fuses are installed.
- The integral o-ring seal provides an IPX4 splash-proof rating while ensuring a secure fit to reduce infiltration of dirt and other contaminants.
- Greater mounting flexibility is achieved with the plastic back plate that provides additional isolation from ground sources when mounted on any chassis surface.

Specifications

ATC fuse

Catalog no.	Poles	Terminals	Max amps per block	Max volts/amps per circuit	Wire range per circuit*	UPC	Quantity per shelf carton	Quantity per master carton
BP/FB4-ATC	4	1/4" quick connect	30	32 V/15 A	#12-16	051712527972	5	50
BP/FB6-ATC	6	1/4" quick connect	45	32 V/15 A	#12-16	051712531573	5	50
BP/FB8-ATC	8	1/4" quick connect	60	32 V/15 A	#12-16	051712531580	5	50
BP/FB10-ATC	10	1/4" quick connect	90	32 V/15 A	#12-16	051712531597	5	50

ATM mini-fuse

Catalog no.	Poles	Terminals	Max amps per block	Max volts/amps per circuit	Wire range per circuit*	UPC	Quantity per shelf carton	Quantity per master carton
BP/FB4-ATM	4	1/4" quick connect	30	32 V/15 A	#12-16	051712531603	5	50
BP/FB6-ATM	6	1/4" quick connect	45	32 V/15 A	#12-16	051712531788	5	50
BP/FB8-ATM	8	1/4" quick connect	60	32 V/15 A	#12-16	051712531795	5	50
BP/FB10-ATM	10	1/4" quick connect	90	32 V/15 A	#12-16	051712531801	5	50

ATR micro-fuse

Catalog no.	Poles	Terminals	Max amps per block	Max volts/amps per circuit	Wire range per circuit*	UPC	Quantity per shelf carton	Quantity per master carton
BP/FB4-ATR	4	1/4" quick connect	30	32 V/15 A	#12-16	051712531818	5	50
BP/FB6-ATR	6	1/4" quick connect	45	32 V/15 A	#12-16	051712531825	5	50
BP/FB8-ATR	8	1/4" quick connect	60	32 V/15 A	#12-16	051712531832	5	50
BP/FB10-ATR	10	1/4" quick connect	90	32 V/15 A	#12-16	051712531849	5	50

*Wire size dependant on length of run

#16 up to 10 feet

#14 up to 20 feet

#12 up to 25 feet

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

Bussmann Division
114 Old State Road
Ellisville, MO 63021
United States
Eaton.com/bussmannseries

For Eaton's Bussmann series product information, call **1-855-287-7626** or visit: Eaton.com/BussmannConsumer