

CD 60X25 4/6 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Well-structured and protected wiring provides the basis for installation, maintenance, and safe operation. Those requirements apply in particular for explosion-protected areas. According to DIN EN 60079-14 these wiring ducts are suitable for cables containing intrinsically safe circuits.

General ordering data

Version	60 mm x 25 mm, 4.00 mm x 6.00 mm, 2000 mm
Order No.	2662600000
Type	CD 60X25 4/6 BL
GTIN (EAN)	4050118685169
Qty.	40 m
Delivery status	This article will no longer be available in the future.
Available until	2025-12-31

CD 60X25 4/6 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	60 mm	Height (inches)	2.362 inch
Width	25 mm	Width (inches)	0.984 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	355 g		

Temperatures

Operating temperature range	-5...60 °C
-----------------------------	------------

General information

Colour	blue	Halogen	Yes
Included in delivery	Cable duct, Lid	Lid	Yes
Material	PVC / lead-free	Operating temperature range	-5...60 °C
Slit gap	6 mm	Slit width	4 mm
Standards	In accordance with DIN EN 50085	UL 94 flammability rating	V-0
Version of side panel	slotted		

Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ETIM 9.0	EC000012
ETIM 10.0	EC000012	ECLASS 9.1	27-40-07-03
ECLASS 10.0	27-40-07-03	ECLASS 11.0	27-40-07-03
ECLASS 12.0	27-40-07-03	ECLASS 13.0	27-40-07-03
ECLASS 14.0	27-40-07-03	ECLASS 15.0	27-40-07-03

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Catalogues	Catalogues in PDF-format
------------	--

CD 60X25 4/6 BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Rivet and cover

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



General ordering data

Type	EXRV-T 6.5	Version
Order No.	2562710000	Expanding-rivet tool
GTIN (EAN)	4050118571615	
Qty.	4 pc(s).	
Type	EXRV-T 4.5	Version
Order No.	2562720000	Expanding-rivet tool
GTIN (EAN)	4050118571578	
Qty.	4 pc(s).	
Type	EXRV 4.5	Version
Order No.	2562700000	Expanding rivet, 27.5 mm x
GTIN (EAN)	4050118571622	
Qty.	1,000 pc(s).	
Type	EXRV 6.5	Version
Order No.	2562690000	Expanding rivet, 32 mm x
GTIN (EAN)	4050118571639	
Qty.	1,000 pc(s).	

Side arm

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



General ordering data

Type	CD-RETA	Version
Order No.	2554080000	Cable duct binder arm, 8 mm x 115.3 mm
GTIN (EAN)	4050118564204	
Qty.	100 pc(s).	

CD 60X25 4/6 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Marking**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Type	CD-LBK	Version
Order No.	2554120000	Cable duct tag rail kit, 30 mm x
GTIN (EAN)	4050118564242	
Qty.	20 pc(s).	
Type	CD-LBH	Version
Order No.	2562850000	Cable duct tag rail holder, 30 mm x
GTIN (EAN)	4050118571691	
Qty.	150 pc(s).	
Type	CD-LB	Version
Order No.	2562680000	Cable duct tag rail, 15 mm x
GTIN (EAN)	4050118571646	
Qty.	150 pc(s).	