

# Marketing Bulletin

**JAE**  
MB - 456

April 30, 2024

JAE Electronics, Inc. · 142 Technology Drive #100 Irvine, CA 92618 · Ph. (949) 753-2600 · [www.jae.com](http://www.jae.com)

## New Product Line Release: Crimped Wires



JAE has a new line of crimped wires for rapid prototyping of JAE cable connectors. We selected several of our most popular product lines and the most popular wire types to create these new products. They are available for purchase through our regular distribution partners.

The reason for creating these crimped wires is to allow new customers to quickly test and evaluate JAE's cable connectors without having to source the crimp terminal, crimp tool, and wires separately. Our customers can now purchase the crimped wire as a single part number that is ready to be inserted into the appropriate connector housing.

Search for inventory of crimped wires through our [Distributor Stock Search](#)

JAE P/N	Wire Size	Wire Type	Wire Length	Crimp Terminal Used	Compatible Connector Housing Options
C2777-M19P09K3F2-AWG20-900	AWG 20	TXL	900mm	M19P09K3F2	MX19002P51, MX19004P51, MX19002P52, MX19004P52
C2777-MX19S10K451-FB0.5-900	0.5mm <sup>2</sup>	FLRY-B	900mm	MX19S10K451	MX19002S51, MX19004S51, MX19002S52, MX19004S52, MX19A002S53, MX19A003S51
C2777-M23S05K351-AV0.5-900	0.5mm <sup>2</sup>	AVSS	900mm	M23S05K351	MX23A12SF1, MX23A18SF1, MX23A26SF1, MX23A34SF1, MX23A40SF1
C2777-MX19P10K451-FB0.5-900	0.5mm <sup>2</sup>	FLRY-B	900mm	MX19P10K451	MX19002P51, MX19004P51, MX19002P52, MX19004P52, MX19A002P53
C2777-MX80P10K4F1-FB0.5-900	0.5mm <sup>2</sup>	FLRYW-B	900mm	MX80P10K4F1	MX80B02PZ1A, MX80B02PZ1B, MX80B02PZ1C, MX80B03PZ1A, MX80B04PZ1A, MX80B04PZ1B, MX80B04PZ1C, MX80D04PZ1A
C2777-MX80S08K4F1-FB0.5-900	0.5mm <sup>2</sup>	FLRYW-B	900mm	MX80S08K4F1	MX80A02SZ1A, MX80A02SZ1B, MX80A02SZ1C, MX80A03SZ1A, MX80A03SZ1B, MX80A04SZ1A, MX80A04SZ1B, MX80A04SZ1C, MX80A06SZ1A, MX80A06SZ1B, MX80A06SZ1C, MX80E04SZ1A

<b>C2777-FI-C3-A1-AWG30-300</b>	AWG 30	UL1571	300mm	FI-C3-A1- 15000	FI-S20S, FI-S6S, FI-S8S, FI-S5S, FI-W17S, FI-W9S, FI-W21S (FI-S**S, FI-W**S)
<b>C2777-FI-XC3B-1-AWG30-300</b>	AWG 30	UL1571	300mm	FI-XC3B-1-15000	FI-X30H, FI-X30HL, FI-X30HL-B
<b>C2777-M19S09K3F2-AWG20-900</b>	AWG 20	TXL	900mm	M19S09K3F2	MX19002S51, MX19004S51, MX19002S52, MX19004S52
<b>C2777-JN1-22-22S-AWG22-900</b>	AWG 22	UL2464	900mm	JN1-22-22S- 10000	JN1DS10SL2, JN1FS10SL2, JN2DS10SL2-R, JN2FS10SL2R, JN2DS10SLK-R, JN1DS10SLK
<b>C2777-JN1-22-22P-AWG22-900</b>	AWG 22	UL2464	900mm	JN1-22-22P- 10000	JN1HS10PL2S, JN2HS10PL2, JN1KS10PL2

If you have any questions regarding this matter, please contact your JAE account manager.  
Thank you for your cooperation.

