

PZ 4 ZERT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Crimping tool for wire-end ferrules, 0.5mm ² , 4mm ² , Trapezoidal crimp
Order No.	9017300000
Type	PZ 4 ZERT
GTIN (EAN)	4008190279318
Qty.	1 pc(s).
Replacement parts	9012540000 9202810000

PZ 4 ZERT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Net weight	464 g		

Technical data

Description of article	(1)Crimping tool	Version	Mechanical, without interchangeable inserts
------------------------	------------------	---------	---

Description of contact

Conductor cross-section, max. AWG	AWG 12	Conductor cross-section, min. AWG	AWG 21
Crimping range, max.	4 mm ²	Crimping range, min.	0.5 mm ²
Type of contact	Wire-end ferrules with/without plastic collars		

tool data crimping

Crimping type/profile	Trapezoidal crimp	Drive	mechanical
Wire end ferrules cross-section, max.	4 mm ²		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11
ECLASS 13.0	21-04-38-11	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Downloads

Engineering Data	CAD data – STEP
User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

PZ 4 ZERT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

