

Cable Drag Chain Systems

Murrplastik Cable Drag Chain Systems have proven their quality and longevity under extreme constant loads and environmental influences. Quick delivery and reasonable prices.

MP 18.1 Series Drag Chain



Length: 1 meter/30 links

Assembled 1-meter length Part Number	Inside Height	Inside Width	Outside Width	Radius
0181-01-015-028-0-0-990	18	15	28	28
0181-01-015-048-0-0-990	18	15	28	48
0181-01-015-078-0-0-990	18	15	28	78
0181-01-025-028-0-0-990	18	25	38	28
0181-01-025-048-0-0-990	18	25	38	48
0181-01-025-078-0-0-990	18	25	38	78
0181-01-037-028-0-0-990	18	37	50	28
0181-01-037-048-0-0-990	18	37	50	48
0181-01-037-078-0-0-990	18	37	50	78
0181-01-050-028-0-0-990	18	50	63	28
0181-01-050-048-0-0-990	18	50	63	48
0181-01-050-078-0-0-990	18	50	63	78
0181-01-070-028-0-0-990	18	70	78	28
0181-01-070-048-0-0-990	18	70	78	48

Male Bracket

Part Number
018100004900
018100004900
018100004900
018100005300
018100005300
018100005300
018100005500
018100005500
018100005500
018100005700
018100005700
018100005700
018100005900
018100005900

Female Bracket

Part Number
018100004800
018100004800
018100004800
018100005200
018100005200
018100005200
018100005400
018100005400
018100005400
018100005600
018100005600
018100005600
018100005800
018100005800



Separator

Part Number
018200009000
018200009000
018200009000
018200009000
018200009000
018200009000
018200009000
018200009000
018200009000
018200009000
018200009000
018200009000
018200009000
018200009000

*bracket images may vary slightly from actual products




Create your
own chain



Follow for more
of our chains

MP 3000 Series Drag Chain





Length: 1 meter/22 links

Assembled 1-meter length Part Number	Inside Height	Inside Width	Outside Width	Radius	Male Bracket Part Number	Female Bracket Part Number	Separator Part Number
0300-02-037-050-0-0-990	26	37	55	50	030000008300	030000008200	030000009200
0300-02-037-095-0-0-990	26	37	55	95	030000008300	030000008200	030000009200
0300-02-037-120-0-0-990	26	37	55	120	030000008300	030000008200	030000009200
0300-02-037-150-0-0-990	26	37	55	150	030000008300	030000008200	030000009200
0300-02-056-050-0-0-990	26	56	74	50	030000007700	030000007600	030000009200
0300-02-056-095-0-0-990	26	56	74	95	030000007700	030000007600	030000009200
0300-02-056-120-0-0-990	26	56	74	120	030000007700	030000007600	030000009200
0300-02-056-150-0-0-990	26	56	74	150	030000007700	030000007600	030000009200
0300-02-076-050-0-0-990	26	76	94	50	030000007900	030000007800	030000009200
0300-02-076-095-0-0-990	26	76	94	95	030000007900	030000007800	030000009200
0300-02-076-120-0-0-990	26	76	94	120	030000007900	030000007800	030000009200
0300-02-076-150-0-0-990	26	76	94	150	030000007900	030000007800	030000009200
0300-02-101-050-0-0-990	26	101	119	50	030000008900	030000008800	030000009200
0300-02-101-095-0-0-990	26	101	119	95	030000008900	030000008800	030000009200
0300-02-101-120-0-0-990	26	101	119	120	030000008900	030000008800	030000009200
0300-02-101-150-0-0-990	26	101	119	150	030000008900	030000008800	030000009200

*bracket images may vary slightly from actual products

MP 45.1 Series Drag Chain



Length: 1 meter/15 links

Assembled 1-meter length Part Number	Inside Height	Inside Width	Outside Width	Radius	Male Bracket Part Number	Female Bracket Part Number	Strain Relief Part Number	Separator Part Number
0451-01-75-125-0-2-1005	45	75	95	125	0450007551	0450007550	0451075010	045000009200
0451-01-75-150-0-2-1005	45	75	95	150	0450007551	0450007550	0451075010	045000009200
0451-01-75-200-0-2-1005	45	75	95	200	0450007551	0450007550	0451075010	045000009200
0451-01-100-125-0-2-1005	45	100	120	125	0450010051	0450010050	0451100010	045000009200
0451-01-100-150-0-2-1005	45	100	120	150	0450010051	0450010050	0451100010	045000009200
0451-01-100-200-0-2-1005	45	100	120	200	0450010051	0450010050	0451100010	045000009200
0451-01-150-125-0-2-1005	45	150	170	125	0450015051	0450015050	0451150010	045000009200
0451-01-150-150-0-2-1005	45	150	170	150	0450015051	0450015050	0451150010	045000009200
0451-01-150-200-0-2-1005	45	150	170	200	0450015051	0450015050	0451150010	045000009200

*bracket images may vary slightly from actual products

