

**SPECIFICATIONS**

Antenna Model	S3307BPNF
Operating Frequency (GHz)	3.3-3.8
Peak Gain (dBi)	9.0
Vertical Plane 3 dB Beamwidth	8°
Azimuth Plane 3 dB Beamwidth	Omni
Weight – kg (lb.)	0.52 (1.15)
Height – cm (in.)	71.63 (28.2)
Polarization	Linear Vertical
VSWR – Max	2.0:1
Max Power - Ambient 25°C (W)	10
Enclosure	Polycarbonate
RF Connector	N(f)




**SAFETY**

This antenna is designed to mount to an outdoor pole or mast. To prevent personal injury or equipment damage, the antenna must be securely mounted per the instructions.

**MOUNTING**

The M8 metric U-bolts mounting bracket accommodates a 3.2-5.4 centimeter (1.25"-2.125") mast. Make sure that the mast does not extend above the metal base on the omni. If multiple antennas are mounted on the same mast, it is important to place this antenna at least 30 centimeters (12 inches) from the others to keep interaction to a minimum.




**LOCATION**

The location of the antenna is important. Best performance is achieved when transmit and receive antennas are mounted at the same height and in a direct line of sight with no obstructions. If this is not possible and reception is poor, try different mounting positions to optimize reception.

**CONNECTOR ATTACHMENT**

The antenna has a female N-connector which provides great flexibility during installation. Weatherproof the connectors and attach the feedline to the mast with cable ties or tape.



**✓RoHS**

[sales@lairdconnect.com](mailto:sales@lairdconnect.com)  
[support@lairdconnect.com](mailto:support@lairdconnect.com)  
[www.lairdconnect.com](http://www.lairdconnect.com)

Laird warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations Laird will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the Laird product is installed. Useful lifetime of the original end product may vary but is not to exceed five (5) years from the original date of the end product purchase.

Any information furnished by Laird Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird materials rests with the end user, since Laird and its agents cannot be aware of all potential uses. Laird makes no warranties as to the fitness, merchantability or suitability of any Laird materials or products for any specific or general uses. Laird shall not be liable for incidental or consequential damages of any kind. All Laird products are sold pursuant to the Laird Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request.

© Copyright 2019 Laird Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Logo, and other marks are trademarks or registered trademarks of Laird Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird or any third party intellectual property rights.

