


Industry Applications.



Bulgin is widely recognised as a leading manufacturer of environmentally sealed connectors & components.

With over 95 years of experience in the industry, Bulgin continues to innovate & develop products and services to cater for its global customer base across a variety of markets.

Recreation & Leisure.



Our robust connectivity solutions power water features in some of the world's most renowned hotels and amusement parks. But that's not where our sealed capabilities end. We also have numerous sealed switches and fuse holders in operation worldwide to compliment systems utilising our watertight connectors and provide a truly comprehensive sealed solution.

Whether you require a waterproof power connector for outdoor events and productions or interface components for electrical appliances, we are sure to have the suitable solution for your design and development needs.



Water Systems.

Whether indoor or outdoor, water systems such as swimming pools and water fountains require highly ruggedized and sealed solutions. Our robust connectivity solutions power water features in some the world's most renowned hotels and amusement parks.

But that's not where our sealed capabilities end. We also have numerous sealed switches and fuse holders in operation worldwide to compliment systems utilising our watertight connectors and provide a truly comprehensive sealed solution.

- Water & Light Show Equipment
- Robot Pool Cleaning Equipment
- Motorised Swimming Pool Cover
- High End Jacuzzi
- Water Quality System
- Hotel Water Fountains
- Filtration Box
- Pool Heating Equipment



Products Related To This Industry:

Rocker Switches

Switches



- Ratings from 10A, 250Vac - 20A, 277Vac
- Push-on, solder & PCB terminals
- Splash resistant & antimicrobial options
- Illuminated & Non-illuminated options
- Large selection of sizes & styles

900 Series

Circular Power Connectors



- 32A, 600V ac/dc max rating
- 2, 3, 4, 5, 7 & 10 contacts
- IP66, IP67, IP68 & IP69K protection
- Single or 3 phase applications
- CCC, UL, CSA & VDE approvals

Standard Ethernet

Circular Data Connectors



- Cat5e RJ45 Ethernet Connectors
- Data rates up to 100MHz
- IP66, IP67, IP68 & IP69K protection
- Shielded system
- Noise immunity & EMI protection

6000 Series

Circular Power Connectors



- 2 - 22 Contacts
- Plastic or Metal Housing
- IP66, IP67, IP68 & IP69K protection
- Secure, quick mating / release
- cULus, UL, VDE Approvals

Standard Series

Circular Power Connectors



- Rating up to 12A, 277V ac/dc
- 2, 3, 4, 6, 7, 9, 12 & 25 contacts
- IP66, IP67, IP68 & IP69K protection
- Plug & receptacle connectors
- CCC, UL, CSA & VDE approvals

Fuse Holders

Fuse Holders



- In-line, panel, PCB & base mounting
- Screw or snap fit variants
- PC1, PC2 & PC3 shock protection
- IP66, IP67 & IP68 sealed versions
- Ideal for 5x20mm & 6.3x32mm fuse sizes

Entertainment & Hospitality.

Power connections and switches are fundamental for activating and controlling a variety of electronic equipment in entertainment and hospitality applications. Whether you require a waterproof power connector for outdoor events and productions or interface components for electrical appliances, we are sure to have the suitable solution for your design and development needs.

- Water Show Equipment & Motors
- Popcorn Machines
- Vending Machines
- Roulette Machines
- Event and Stage Lighting
- Pool Cleaning Robots
- Electronic Scoreboards
- Champagne Dispensers



Products Related To This Industry:

Rocker Switches

Switches



- Ratings from 10A, 250Vac - 20A, 277Vac
- Push-on, solder & PCB terminals
- Splash resistant & antimicrobial options
- Illuminated & Non-illuminated options
- Large selection of sizes & styles

IEC Connectors

IEC Connectors



- IEC Connectors, Inlets & Outlets
- EC & EN 60320 Standards
- UL, CSA, VDE & CE approved
- C13, C14, C15, C16, C18, C19 & C20 as well as Sheet E, F, H, I & J types

Vandal Resistant Switches

Switches



- High corrosion resistance
- Domed, low & prominent profiles
- IP66 & IP68 sealing versions
- Illuminated & non-illuminated
- Front & rear panel mount versions

Standard Series

Circular Power Connectors



- Rating up to 12A, 277V ac/dc
- 2, 3, 4, 6, 7, 9, 12 & 25 contacts
- IP66, IP67, IP68 & IP69K protection
- Plug & receptacle connectors
- CCC, UL, CSA & VDE approvals

900 Series

Circular Power Connectors



- 32A, 600V ac/dc max rating
- 2, 3, 4, 5, 7 & 10 contacts
- IP66, IP67, IP68 & IP69K protection
- Single or 3 phase applications
- CCC, UL, CSA & VDE approvals

400 Series

Circular Power Connectors



- Ratings up to 8A, 250V ac/dc
- 2, 3, 4, 6, 8, 10 & 12 contacts
- IP66, IP67, IP68 & IP69K protection
- Pin or socket, screw thread locking
- CE, UL, CSA & VDE approvals

4000 Series

Circular Power Connectors



- Ratings up to 13A, 600V ac/dc
- 2, 3, 4, 6, 8, 10 & 12 Contacts
- IP66, IP67, IP68 & IP69K protection
- Pin or socket, bayonet locking
- UL, CSA & VDE approvals

Bulgin has you covered.

**Our components are available through a
large network of National and International
Distributors Worldwide.**

Search for stock at:

www.bulgin.com/products/stock



www.bulgin.com

Europe

Bulgin
200 Cambridge Science Park
Milton Road
Cambridge, CB4 0GZ, UK
tel: +44 (0) 1803 407757
e: info@bulgin.com

Americas

Bulgin
11849 Telegraph Road
Santa Fe Springs
CA 90670, USA
tel: +1 760-343-3650
e: info@bulgin.com

Asia Pacific

Bulgin
11849 Telegraph Road
Santa Fe Springs
CA 90670, USA
tel: +1 760-343-3650
e: info@bulgin.com