




Industry Applications.



Bulgin is widely recognised as a leading manufacturer of environmentally sealed connectors & components.

With over 95 years of experience in the industry, Bulgin continues to innovate & develop products and services to cater for its global customer base across a variety of markets.

Renewable Energy.

Renewable energy technologies operate in some of the harshest environments on the planet. Extreme temperatures, UV exposure, vibrations and water all pose complex challenges in establishing and keeping renewable energy systems operational. With more moving parts than other renewable energy systems, wind turbines in particular require extremely robust connectors to cope with such extreme conditions.



Renewable Energy.

Thoroughly tested and designed specifically to operate reliably in harsh conditions, Bulgin's rugged power and data connectors are the ideal solutions for green and renewable energy applications including wind and solar energy systems.

- Solar Power Inverters
- Wind Turbine Vibration
- Monitoring System
- Solar Lighting Panels
- Solar Water Pump Controller
- Solar Battery Enclosures
- Solar PV Combiner Boxes



Products Related To This Industry:

Standard Series

Circular Power Connectors



- Rating up to 12A, 277V ac/dc
- 2, 3, 4, 6, 7, 9, 12 & 25 contacts
- IP66, IP67, IP68 & IP69K protection
- Plug & receptacle connectors
- CCC, UL, CSA & VDE approvals

Standard Ethernet

Circular Data Connectors



- Cat5e RJ45 Ethernet Connectors
- Data rates up to 100MHz
- IP66, IP67, IP68 & IP69K protection
- Shielded system
- Noise immunity & EMI protection

400 Series

Circular Power Connectors



- Ratings up to 8A, 250V ac/dc
- 2, 3, 4, 6, 8, 10 & 12 contacts
- IP66, IP67, IP68 & IP69K protection
- Pin or socket, screw thread locking
- CE, UL, CSA & VDE approvals

4000 Series

Circular Power Connectors



- Ratings up to 13A, 600V ac/dc
- 2, 3, 4, 6, 8, 10 & 12 Contacts
- IP66, IP67, IP68 & IP69K protection
- Pin or socket, bayonet locking
- UL, CSA & VDE approvals

900 Series

Circular Power Connectors



- 32A, 600V ac/dc max rating
- 2, 3, 4, 5, 7 & 10 contacts
- IP66, IP67, IP68 & IP69K protection
- Single or 3 phase applications
- CCC, UL, CSA & VDE approvals

6000 Series

Circular Power Connectors



- 2 - 22 Contacts
- Plastic or Metal Housing
- IP66, IP67, IP68 & IP69K protection
- Secure, quick mating / release
- cULus, UL, VDE Approvals

Bulgin has you covered.

**Our components are available through a
large network of National and International
Distributors Worldwide.**

Search for stock at:

www.bulgin.com/products/stock



www.bulgin.com

Europe

Bulgin
200 Cambridge Science Park
Milton Road
Cambridge, CB4 0GZ, UK
tel: +44 (0) 1803 407757
e: info@bulgin.com

Americas

Bulgin
11849 Telegraph Road
Santa Fe Springs
CA 90670, USA
tel: +1 760-343-3650
e: info@bulgin.com

Asia Pacific

Bulgin
11849 Telegraph Road
Santa Fe Springs
CA 90670, USA
tel: +1 760-343-3650
e: info@bulgin.com