

New Product Introduction		Date
Product	Announcing Digi IX15	

Audience	All Digi <a href="#">XBee</a> ® and cellular router product distributors
----------	--

Product Notice	Digi is pleased to announce the release of the Digi IX15 gateway and cellular router. General availability of new SKUs is May 11, 2021.
----------------	---

<b>Product Description</b>   <i>Digi IX15</i>	<p>The versatile Digi IX15 functions as both XBee® gateway and cellular router for customers seeking lower-cost, quicker-to-market alternatives to chip-down DIY designs for networking operations. The industrial-grade Digi IX15 helps build Digi XBee® or other cellular networks – with Python programming for edge computing – for connectivity to cloud applications or data centers.</p> <p>With C1D2 certification and rugged enclosure, Digi IX15 is ideal for the harsh, corrosive environments found in oil and gas, water/wastewater, solar, agriculture and other industrial applications. For developers needing a highly secure, common platform to cut costs and time-to-market, Digi IX15 reduces risk and drives project efficiencies.</p> <p>Digi recommends Digi Remote Manager® to manage the IX15 and connected devices. Digi Remote Manager® is a web-based device management platform that allows easy setup, mass configuration and maintenance for thousands of remote devices.</p> <p><b>Features:</b></p> <ul style="list-style-type: none"><li>• 2.4GHz Digi XBee® 3 (Zigbee / DigiMesh / 802.15.4)</li><li>• Cellular (Global LTE Cat-4, 3G, 2G)</li><li>• Edge compute programmability – Python 3</li><li>• Dual SIMs and Digi <a href="#">SureLink</a>®</li><li>• Bluetooth (hardware – 5.0, software – 4.2)</li><li>• 1 x Ethernet (10/100)</li><li>• 1 x Serial Port RS-232/485 (RJ45 10-pin)</li><li>• Operating Temperature -40°C to +74°C</li><li>• Digi <a href="#">TrustFence</a>® security framework</li><li>• Flat surface mounting or optional DIN rail clip</li><li>• Class 1 Division 2 (C1D2) certified</li></ul>
---	--

<b>Cellular Band Support</b>	Coverage: Global LTE Cat 4: B1, B2, B3, B4, B5, B7, B8, B12, B13, B18, B19, B20, B25, B26, B28, B38, B39, B40, B41 3G: B1, B2, B4, B5, B6, B8, B19 2G EDGE / GPRS: 850 / 900 / 1800 / 1900 MHz
------------------------------	---

<b>Cellular Network Certifications</b>	Certified: AT&T In process: Verizon, Bell Visit <a href="https://www.digi.com/resources/certifications">https://www.digi.com/resources/certifications</a> for latest certifications.
--	--

<b>Regional Certifications</b>	U.S. (FCC), Canada, Mexico, Europe (RED and UKCA), Japan Additional certifications in process: Australia, New Zealand Visit <a href="https://www.digi.com/resources/certifications">https://www.digi.com/resources/certifications</a> for latest certifications.
--------------------------------	--

IX15 SKUs	Description	MSRP (Qty 1)
IX15-00G4-XB2	Digi IX15 - LTE CAT-4, XBee® 3 2.4GHz No Accessories	\$499
IX15-00G4-XBP2	Digi IX15 - LTE CAT-4, XBee® 3 2.4GHz PRO, No Accessories	\$499

Digi Remote Manager SKUs	Description	MSRP (Qty 1)
DIGI-RM-STD-1YR	Digi Remote Manager Standard - 1 Year Edition	\$29.00
DIGI-RM-PRM-1YR	Digi Remote Manager Premier - 1 Year Edition	\$48.00
DIGI-RM-PRM-3YR	Digi Remote Manager Premier - 3 Year Edition	\$126.00
DIGI-RM-PRM-5YR	Digi Remote Manager Premier - 5 Year Edition	\$210.00

Accessory SKUs	Description	MSRP (Qty 1)
76002107	IX15 2.4GHz Accessory Kit	\$132.00
76002104	Power supply with plug tips for US, UK, EU, AU	\$59.00
DC-ANT-24DT	(1) Magnetic table-top 2.4 GHz antenna	\$30.00
76002103	(1) Cellular antenna (order quantity 2)	\$9.99
76002106	CAT6 patch cable, 2 meter (6 feet), black, flat	\$9.99
76002095	DIN rail clip kit	\$4.99
76000645	Connect EIA 422/485 devices to Digi products that have 10-pin RJ-45 connectors*	\$25.30

\*For RS-232 cabling pinouts and recommended cables, please refer to the Digi products cabling guide at:  
[www.digi.com/resources/documentation/Digidocs/PDFs/90000253.pdf](https://www.digi.com/resources/documentation/Digidocs/PDFs/90000253.pdf)

<b>Authorization</b>	Digi International Product Management
----------------------	---------------------------------------